





- 1 FOR 1.27 [.050] TO 2.08 [.082] WIRE INSULATION DIA
- 2 TONGUE MATERIAL THK: 0.46±0.05 [.018±.002]
- 3 APPLIES FROM THE METAL EDGE OF THE BARREL TO THE CENTER OF THE STUD
- 4 NOTE DELETED

100	LOOSE PC, BOX	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545) INSULATION: NYLON COLOR: YELLOW (ASTM-D4066) TYPE 1	8-324075-1
4000	324075 ON TAPE		2-324075-1
1	WIRE TERMINAL		324075
QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 27AUG09	 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK JEFF RUTH 27AUG09		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TOM MICHIELUTTI 27AUG09		
	0 PLC ± -	PRODUCT SPEC	NAME WIRE TERMINAL PIDG - RING TONGUE WIRE SIZE: 26-22	
	1 PLC ± -	APPLICATION SPEC		
	2 PLC ± -	WEIGHT		
MATERIAL SEE TABLE	3 PLC ± 0.20 [.008]	CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779
	4 PLC ± -		DRAWING NO C-324075	RESTRICTED TO -
	ANGLES ± 5°		SCALE 10:1	SHEET 1 OF 1
FINISH SEE TABLE		REV G3		