
molex



Part Number : 1720641004
Product Description : Mega-Fit Right-Angle Header, 5.70mm Pitch, Through Hole, Dual Row, 4 Circuits, 0.76µm Gold (Au) Plating, 3.60mm Tail Length, Glow-Wire Capable, Tray, Black
Series Number : 172064
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : 172064-1002

Documents and Resources

Drawings

1720641004_sd.pdf

768250001-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

SYM-172064-1004-001.zip

Specifications

AS-76823-100-001.pdf

1720631000-PS-000.pdf

PS-76823-100-001.pdf

1720631000-TS-000.pdf

TS-76823-100-001.pdf

TS-76825-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33

Downloaded from Arrow.com.

China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	172064
Description	Mega-Fit Right-Angle Header, 5.70mm Pitch, Through Hole, Dual Row, 4 Circuits, 0.76µm Gold (Au) Plating, 3.60mm Tail Length, Glow-Wire Capable, Tray, Black
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Mega-Fit
UPC	887191558929

Agency

Downloaded from Arrow.com.

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	23.5A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Gender	Male
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	16.78mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Mounting Style	Through Hole
Net Weight	2.838/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm, 2.36mm
PC Tail Length	3.60mm
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Plating min - Mating	0.762µm

Downloaded from Arrow.com.

Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Temperature Range - Operating	-40° to +120°C
Termination Interface Style	Through Hole
Unmated Height	14.53mm

Solder Process Data

Max-Duration	30
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mega-Fit Dual Row Receptacle Housings	170001
Mega-Fit Dual Row Receptacle Housings	171692
Mega-Fit-to-Mega-Fit Off-the-Shelf (OTS) Overmolded Cable Assemblies	245136

Downloaded from Arrow.com.