
CLIFF

CAT.6A SHIELDED RJ45 FEEDTHROUGH CONNECTOR





Feedthrough Features

- Fits standard XLR Ø24mm cutout.
- No soldering or punch termination. Use standard cable for each connector style.
- Front or rear mounted.
- Low rear profile

General:

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

Material:

1.RJ45 In-Line Coupler:
PC/ABS, UL 94V-0, Black colour
2.RJ45 In-Line Coupler Contact:
Phosphor Bronze, 3-50 micro inches gold plating over nickel plate.
3.PCB: FR4, UL 94V-0
4. Plastic Frame: Polyamide UL94 V-2
5. Metal Frame: Diecast, Black or Nickel plated

Performance:

1.T568A & T568B wiring.
2.Meet ISO/IEC 11801 and EN50173
3.Meet ANSI/TIA/EIA 568B.2
4.Operating temperature: Min -10°C Max +70°C

Other models available:

Part No.	
CP30225S	Cat.6A Shielded RJ45 Black plastic frame, CSK holes
CP30225SM	Cat.6A Shielded RJ45 Nickel plated metal frame, CSK holes
CP30225SM3	Cat.6A Shielded RJ45 Nickel plated metal frame, M3 holes
CP30225SMB	Cat.6A Shielded RJ45 Black metal frame, CSK holes
CP30225SM3B	Cat.6A Shielded RJ45 Black metal frame, M3 holes
CP30225SX	Cat.6A Shielded RJ45 Black plastic frame, PLAIN holes

© CLIFF 07/2020 ISS.2

For further information, contact sales@cliffuk.co.uk

Cliff Electronic Components Limited,
76 Holmethorpe Avenue, Holmethorpe Ind. Estate,
Redhill, Surrey RH1 2PF U.K.
Tel: +44 (0)1737 771375 Fax: +44 (0)1737 766012

www.cliffuk.co.uk

✓RoHS

Downloaded from Arrow.com.