Part Number : 760205004
Product Description : GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Right Guide 7 Row, 4 Columns, 56 Circuits, Lead-Free
Series Number : 76020
Status : Active
Product Category : Backplane Connectors



Documents and Resources

Drawings

760205004_sd.pdf

PK-70873-607-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-45499-002-001.pdf

PS-75710-999-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	76020
Description	GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Right Guide 7 Row, 4 Columns, 56 Circuits, Lead-Free
Application	Coplanar, Daughtercard
Component Type	PCB Receptacle
Product Name	GbX I-Trac
UPC	822350969338

Agency

UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Data Rate	12.0 Gbps
Real Signals (per 25mm)	48
Shielded	No
Shield Type	N/A
Voltage - Maximum	120V AC (RMS)/DC

Downloaded from Arrow.com.

Physical

Circuits (Loaded)	56
Circuits (maximum)	56
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	9.716/g
Number of Columns	4
Number of Pairs	4, Open Pin Field
Number of Rows	7
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.00mm
Pitch - Mating Interface	1.85mm, 3.70mm
Pitch - Termination Interface	1.00mm, 2.70mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-55° to +80°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
GbX I-Trac Vertical Header Modules	76015

Use with Part(s)

Description	Part Number
GbX I-Trac Right-Angle Headers	78234
Wide Guide Modules and Pins	76153

Application Tooling

This document was generated on Apr 27, 2026

Downloaded from Arrow.com.