



REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	JUN23/06	L.CHAN

MATERIALS:

- HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL94V-0
COLOR: BLACK
- CONTACTS: PHOSPHOR BRONZE
- PLATING: REFER TO PART NUMBER FOR GOLD THICKNESS
ON MATING SURFACE
50 MICROINCH [1.27 MICRONS] MIN. NICKEL OVERALL
100 MICROINCH [2.54 MICRONS] MIN. MATTE-TIN
OR GOLD FLASH OVER TAIL
- SHIELD: COPPER ALLOY WITH NICKEL PLATED
- RECOMMENDER SOLDERING TEMPERATURE:
WAVE SOLDERING OR REFLOW SOLDERING AT 260°C MAXIMUM FOR 5 SEC MAXIMUM



PART NUMBER: R J E 0 6 - 1 8 8 - 1 X 2 0 H

SERIES: R J E 0 6 - 1 8 8 - 1 X 2 0 H

1 PORT: 1 8 8 - 1 X 2 0 H

NO. OF POSITIONS: 1 8 8 - 1 X 2 0 H

NO. OF CONTACTS: 1 8 8 - 1 X 2 0 H

HIGH TEMPERATURE MATERIAL
WITH FLANGE
GOLD PLATING
1 = 6 MICROINCH
2 = 15 MICROINCH
3 = 30 MICROINCH
4 = 50 MICROINCH
FULL SHIELD

DRAWN PAULW		DATE JUN23/06		Amphenol Canada Corp.							
DESIGNED											
CHECKED CHIGOW		JUN23/06		TITLE RJE06 SERIES, 8 POSITION 8 CONTACT, VERTICAL MOUNT, WITH SHIELD, AND FLANGE - RoHS COMPLIANT							
I. E. APPRD.											
Q. A. APPRD.											
DWG. APPRD.											
ENG. REL. NO.		DWG		DRAWING NO. P-RJE06-188-1X20-H		REV. A					
REF.											
DIMENSIONS ARE IN INCHES [mm]		CODE ID. NO. 03554		SCALE		WT. -----		SURF. -----		SHEET 1 OF 1	

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.