



Micro Commercial Components

Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

MPSA63 MPSA64

Features

- Capable of 1.5Watts of Power Dissipation
- Collector Current –500mA
- Operating Junction Temperature Range: -55°C to +150°C
- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0 and MSL Rating 1
- Marking:MPSA63,MPSA64

Maximum Ratings

Symbol	Rating	Rating	Unit
V _{CEO}	Collector-Emitter Voltage	-30	V
V _{CBO}	Collector-Base Voltage	-30	V
V _{EBO}	Emitter-Base Voltage	-10	V
I _C	Collector Current, Continuous	-500	mA
T _J	Operating Junction Temperature	150	°C
T _{STG}	Storage Temperature	-55 to +150	°C

Thermal Characteristics

Symbol	Rating	Max	Unit
P _D	Total Device Dissipation @ T _A =25°C Derate above 25°C	625 5.0	mW mW/°C
P _D	Total Device Dissipation @ T _A =25°C Derate above 25°C	1.5 12	Watts mW/°C
R _{θJC}	Thermal Resistance, Junction to Case	83.3	°C/W
R _{θJA}	Thermal Resistance, Junction to Ambient	200	°C/W

Electrical Characteristics @ 25°C Unless Otherwise Specified


Symbol	Parameter	Min	Max	Units
--------	-----------	-----	-----	-------

OFF CHARACTERISTICS

V _{(BR)CEO}	Collector-Emitter Breakdown Voltage (I _C =-100μAdc, V _{BE} =0)	-30	---	Vdc
I _{CBO}	Collector Cutoff Current (V _{CB} =-30c, I _E =0)	---	-100	nAdc
I _{EBO}	Emitter Cutoff Current (V _{EB} =-0Vdc, I _C =0)	---	-100	nAdc

* Pulse Test: Pulse Width<300us, Duty Cycle<2.0%

PNP Darlington Transistor



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.170	.190	4.33	4.83	
B	.170	.190	4.30	4.83	
C	.550	.590	13.97	14.97	
D	.010	.020	0.36	0.56	
E	.130	.160	3.30	3.96	
G	.096	.104	2.44	2.64	

Symbol	Parameter	Min	Typ	Max	Units
ON CHARACTERISTICS⁽¹⁾					
h_{FE}	DC Current Gain ($V_{CE}=-5.0Vdc$, $I_C=-10mA$)				
		MPSA63	5000	---	---
		MPSA64	10000	---	---
	($V_{CE}=-5.0Vdc$, $I_C=-100mA$)	MPSA63	10000	---	---
		MPSA64	20000	---	---
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage ($I_C=-100mA$, $I_B=-0.1mA$)	---	---	-1.5	Vdc
$V_{BE(on)}$	Base-Emitter On Voltage ($I_C=-100mA$, $V_{CE}=-5.0Vdc$)	---	---	-2.0	Vdc

SMALL-SIGNAL CHARACTERISTICS

f_T	Current-Gain ---Bandwidth Product ⁽²⁾ ($V_{CE}=-5.0Vdc$, $f=100MHz$, $I_C=-100mA$)	125	---	---	MHz
-------	--	-----	-----	-----	-----

1. Pulse Test: Pulse Width<300us, Duty Cycle<2.0%
2. $f_T=h_{fe} \times f_{ies}$

Ordering Information

Device	Packing
(Part Number)-AP	Tape&Reel;2Kpcs/Box
(Part Number)-BP	Bulk;1Kpcs/Bag

IMPORTANT NOTICE

Micro Commercial Components Corp .reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes .
Micro Commercial Components Corp . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp* . and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the expresse written approval of Micro Commercial Components Corporation.