



RDIMM

M393A2K43DB3-CWE



OVERVIEW

SPECIFICATIONS

RELATED RESOURCES

RELATED INSIGHTS

Proven DRAM module solution in the global market

Samsung’s memory modules are designed for a wide range of applications to deliver the best performance with low power requirements.

Specifications

DDR	DDR4	Dimm Type	RDIMM
Density	16 GB	Rank x Org.	2R x 8
Speed	3200 Mbps	Voltage	1.2 V
No. of Pin	288	Component Composition	(1G x 8) x 18
Product Status	Sample		

SEE ALL

Related resources



Handling guide

Related insights



Inside the building blocks of the 5G future

The management and processing of data in the new era of connectivity will be a critical issue for every organization and enterprise.

[LEARN MORE >](#)



Samsung's PM1733 SSD and High Density DIMMs Support AMD

Samsung announced support of the Samsung PM1733 PCIe Gen4 SSD and high density DIMMs for the AMD EPYC™ 7002 Generation Processors.

[LEARN MORE >](#)



All product specifications reflect internal test results and are subject to variations by user's system configuration. All product images shown are for illustration purposes only and may not be an exact representation of the product. Samsung reserves the right to change product images and specifications at any time without notice.

Newsroom

[Product finder](#)

[Technical resources](#)

[TCO calculator](#)

[About us](#)

PRODUCTS

[DRAM](#)

[SSD](#)

[eSTORAGE](#)

[MCP](#)

[PROCESSOR](#)

SOLUTIONS

[APPLICATIONS](#)

[TOPICS](#)

Other Sites

[中文\(简体\)](#)

[B2B Workplace](#)

[Memory \(日本語\)](#)

[ISOCELL](#)

[Exynos](#)

Follow us




IMAGE SENSOR

SECURITY
SOLUTIONS

DISPLAY IC

POWER IC

LED [↗](#)

Display [↗](#)

Worker Safety [↗](#)

Samsung Business [↗](#)

Copyright © 1995-2020 SAMSUNG All Rights Reserved.

PRIVACY

LEGAL

SITEMAP

This website is best viewed using Microsoft Internet Explorer 9 or higher, and/or latest version of Google Chrome and Mozilla Firefox browsers.