

## FO connectors - VS-V1-C-LC-MNNA-PG9-A1-G - 1419190


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



LC fiber optic connector, IP67, with bayonet locking, metal housing, duplex, with adhesive connection technology, for multi-mode fiber, for cable diameter of 5.0 mm ... 10 mm



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 540438
GTIN	4046356540438
Weight per Piece (excluding packing)	140.000 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### Mechanical characteristics

Number of positions	2
Number of slots	1
Locking type	Bayonet locking
Fiber type	Multi-mode 50/125 µm fiberglass
Insertion/withdrawal cycles	500
Connection method	LC
Max. cable diameter	5 mm ... 10 mm
Color	silver
Degree of protection	IP67
Design	LC

#### Ambient conditions

FO connectors - VS-V1-C-LC-MNNA-PG9-A1-G - 1419190

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
---------------------------------	------------------

Material data

Housing material	Zinc die-cast
Material	Metal


Electrical characteristics

Number of positions	2
---------------------	---

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings



Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC B.01742
-------------

