







THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20
©	COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.	

LOC		DIST		REVISIONS				
-	-	R	LTR	DESCRIPTION	DATE	DRN	APVD	
		B		REV PER ECO 12-010940	7-31-12	CT	DH	
		C		ECO-13-004755	26MAR2013	HG	DH	
		D		ECO-14-017030	25NOV2014	MGM	CT	
:								



- ① MATERIAL:
CONTACT - COPPER ALLOY
HOUSING - LCP, COLOR - BLACK
- ② FINISH:
MATING AREA: 1.27 μ m MIN GOLD OVER
1.27 μ m MIN NICKEL
- ③ FINISH:
COMPLIANT PIN AREA: 0.38 μ m MIN BRIGHT TIN LEAD
OVER 1.27 μ m MIN NICKEL
- ④ FINISH:
COMPLIANT PIN AREA: 0.38 μ m MIN MATTE TIN
OVER 1.27 μ m MIN NICKEL
- ⑤ ---
- ⑥ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- ⑦ REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED
PLATING THRU HOLE DIAMETER AND PLATING THICKNESS.

 	2102157-2
 	2102157-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)		DWN 24JUN2009 CHK D. BELACK A. TSANG 6-24-2009 M. MALONIS 6-24-2009		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.01 1 PLC ±.01 2 PLC ±.05 3 PLC ±.01 4 PLC ±.01 ANGLES ±.2°		NAME Fortis Zd, 3-PAIR, 10-COLUMN, VERTICAL, SINGLE MODULE ASSEMBLY	
MATERIAL 		WEIGHT ~ 3.83 g		SIZE A1	
FINISH		APPLICATION SPEC		CAGE CODE	
		114-13267		DRAWING NO	
				C=2102157	
		CUSTOMER DRAWING		SCALE 8:1	
				SHEET 1 OF 1	
				REV D	