



Have a Question?

Chat with a Product
Information Specialist



What can we help you find?



[Products](#)

[Industries](#)

[Resources](#)

[About TE](#)

[Support Center](#)

[My Account](#)

[Home](#) > [Products](#) > [Resistors](#) > [Product Feature Selector](#) > Product Details

404802692040 Product Details

[Share](#)

[Print](#)

[Email](#)



404802692040
(3-1625931-3)

TE Internal Number: 3-1625931-3

[Active](#)

[View 3D PDF](#)

Variable Resistors



[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Variable Resistor
- Resistor Type = Potentiometer
- Resistance Selection = K Ω
- Resistance = 47K Ω
- Power Rating = 2.00 W

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [Spindle Operated Potentiometers - Type M Series - Ty...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version P00K)
- [3D Model](#) (IGES, Version P00K)
- [3D Model](#) (STEP, Version P00K)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Variable Resistor
- [Resistor Type](#) = Potentiometer
- [Element](#) = Cermet
- [Series](#) = M
- [Sealed](#) = Yes
- [Termination Type](#) = PCB Terminations

Electrical Characteristics:

- Resistance Selection (Ω) = K
- [Resistance \(\$\Omega\$ \)](#) = 47K
- [Power Rating \(W\)](#) = 2.00
- [Tolerance \(%\)](#) = 10

Termination Features:

- [Termination Post Orientation](#) = 5.0 x 3.9

Body Features:

- [Shaft Style](#) = Plain, 1"
- [Package, Component Size](#) = 19

Configuration Features:

- [Sections](#) = Single
- [Adjustment Location](#) = Top
- [Adjustment Style](#) = Spindle
- [Operating Function](#) = Single Turn

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Other:

- Brand = Citec

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

