




PRODUCT NUMBER: 1032-1-17-01-32-14-02-0

www.mill-max.com
DATA SHEET



1032-1-17-01-32-14-02-0 SPECIFICATIONS



General Info		Materials		Technical Specs	
Description¹: Receptacle With A Wire Wrap Tail		Shell Material⁴: Brass Alloy		Mechanical life 1,000 Cycles Minimum (Durability) ⁷ :	
Mounting Feature: Press-Fit into a Non-Plated Through Hole (NPTH)		Shell Plating⁵: 200 - 300 μ " Tin/Lead over Nickel		Operating Temperature Range⁸: -55/+125° C	
Mounting Hole²: .057" (1,448mm)		Contact Plating⁶: 10 μ " Gold over Nickel		Maximum Current: Inner Contact Dependent, see Contact Data Below	
Pin Diameter Range: .015"-.026" (0,381-0,660mm)				Maximum Derated Current: Inner Contact Dependent, see Contact Data Below	
Packaging: Packaged in Bulk				Contact Resistance: 10 m Ω Max	
RoHS: No				Shock⁹: No Elect. Discontinuity > 1 μ s @ 50g	
Product Lifecycle³: Active				Vibration¹⁰: No Elect. Discontinuity > 1 μ s @ 10-2000HZ, 20 G	
Country Of Origin: USA					

NOTES:

- 1. Standard Tolerances:
Lengths +/- .005" (0,13)
Diameters: +/- .002" (0,051)
Angles: +/- 2°
- 2. This is a general guideline; your application may require different specifications
- 3. Part is Active and in Production, No Scheduled Obsolescence
- 4. Brass Alloy 360 per ASTM B 16, or 385 per ASTM B455
- 5. TIN/LEAD (93/7) per ASTM B 545 (Appendix X6.3.2.5 to eliminate whisker growth) Bright finish; NICKEL per ASTM B 689, Type 2 (Bright)
- 6. GOLD per ASTM B 488, Type 1 (99.7% min. gold), Code C (130-200 HK {Knoop hardness}), NICKEL per ASTM B 689, Type 2 (Bright)
- 7. Receptacles are capable of 1,000 Minimum insertion/extraction cycles for a broad range of applications. Mating pin size, shape and finish, along with application specific variables, will affect the life of a receptacle contact.
- 8. Per IEC 60512-11-(4,-9,-10,-12)
- 9. Per IEC 60512-6-3: Test 6c: Shock
- 10. Per IEC 60512-6-4: Test 6d: Vibration (sinusoidal)

CONTACT:

#32 CONTACT
FOR .015"-.026" DIAMETER PINS (δ = .009)
6-FINGER (BeCu), GROUP C



The insertion / extraction force characteristics above were derived using a 30 microinch gold-plated contact and polished steel gauge pins having a bullet-shaped tip. The curves represent typical average values; they are best used to compare the differences between similar size contacts and to guide you in selecting one that is suitable for your application. Your results may vary, so for your specification, we encourage you to obtain complimentary samples for your evaluation.

Material	Beryllium Copper	Fingers	6
Compliancy (δ)	0.009	Length	.083" (2,108mm)
Maximum Current	8A @ 30° C Temp. Rise	Maximum Operating Temp @ Max Current	120.00° C
20% De-rated Maximum Current	6.40A	Contact Resistance	10.00mΩ Max
Contact Group	C		

ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance , Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

RELATED LINKS AND DOCUMENTS

- Engineering Notebook: [Introduction to Pin Receptacles](#)
- Environmental Compliance: <https://www.mill-max.com/rohs>