




The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant & per IEC 61249-2-21 for Halogen-Free compliant.

| REVISIONS |         |                                                                                                |            |         |
|-----------|---------|------------------------------------------------------------------------------------------------|------------|---------|
| SYM       | ECN No. | DESCRIPTION                                                                                    | DATE       | BY      |
| AX22      | NA      | ADDED COMPONENT KEEP OUT AREA LIMIT HEIGHT                                                     | 10/31/2019 | JOAN LU |
| AX23      | NA      | UPDATED QTY OF PACKAGE                                                                         | 12/17/2019 | JOAN LU |
| AX24      | NA      | 1.CORRECT DIM J IN TABLE FOR G42VXXXXXXX<br>2.REVISED LATCH HOLE DIMENSION FROM 1.10 TO 1.15MM | 09/02/2020 | JOAN LU |
| AX25      | NA      | RECOMMENDED AIC MATING CARD CHAMFER CHANGE FROM 0.75 TO 0.3                                    | 02/02/2021 | JOAN LU |
| AX26      | NA      | ADDED NOTE ITEM 5                                                                              | 03/02/2021 | JOAN LU |



NOTES:

1. MATERIALS:  
PLASTICS : HIGH TEMPERATURE THERMOPLASTIC UL94-0,COLOR: BLACK  
SHELL : STAINLESS  
CONTACT: COPPER ALLOY
- 2: FINISH  
TERMINAL : CONTACT AREA : SELECTED GOLD PLATING.  
SOLDER AREA : MATTE TIN PLATING 100u"  
UNDER PLATING: NICKEL PLATING 50u"MIN OVER ALL  
SHELL : UNDER PLATING: ELECTROLESS NICKEL PLATING 50u"MIN OVER ALL
- 3.THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS MATERIALS PER DERCTIVE  
2011/65/EU & 2015/863/EU FOR RoHS AND PER IEC 61249-2-21 FOR HALOGEN FREE.
- 4.PRODUCT SPEC REFER TO PS-7681.
- 5.SUPPORT 920HM APPLICATION.

| PART NUMBER  | POS. (N) | DIM. B | DIM. C | DIM. D | DIM. E | DIM. F | DIM. G |
|--------------|----------|--------|--------|--------|--------|--------|--------|
| G42VX1XXXXHR | 38       | 11.68  | 15.00  | 10.80  | 13.50  | 14.55  | 13.55  |
| G42VX5XXXXHR | 50       | 15.28  | 18.60  | 14.40  | 17.10  | 18.15  | 17.15  |
| G42VX2XXXXHR | 74       | 22.48  | 25.80  | 21.60  | 24.30  | 25.35  | 24.35  |








|                                              |                      |             |                                                                                       |                                                                                                 |  |  |                                                                      |                         |  |             |  |  |  |
|----------------------------------------------|----------------------|-------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|--|--|----------------------------------------------------------------------|-------------------------|--|-------------|--|--|--|
| TOLERANCE                                    | DRAWN APPROVALS      |             | DATE                                                                                  | TITLE<br>MINI COOL EDGE 10<br>INTEGRATED CONNECTOR<br>0.6 PITCH, VERTICAL<br>STANDARD. SMT TYPE |  |  | Amphenol®<br><br>Amphenol Corporation<br>Amphenol Taiwan Corporation |                         |  |             |  |  |  |
| X,<br>X.X ±0.30<br>X.XX ±0.20<br>X.XXX ±0.10 | DESIGNED<br>Joan Lu  | 03/02/2021  |  |                                                                                                 |  |  |                                                                      |                         |  |             |  |  |  |
| CHECKED<br>Sondra Sang                       | 03/02/2021           | UNIT<br>mm  |                                                                                       |                                                                                                 |  |  | SIZE<br>A3                                                           | PART No.<br>G42VXXXXXHR |  |             |  |  |  |
| APPROVED<br>Hank Hsu                         | 03/02/2021           | SCALE<br>NA |                                                                                       |                                                                                                 |  |  | SHEET<br>1 OF 8                                                      | DWG No.<br>G42VXXXXXHR  |  | REV.<br>AX2 |  |  |  |
| ANGULAR ±2°                                  | DWG TYPE<br>CUST DWG |             | PROJECT CODE<br>T631                                                                  |                                                                                                 |  |  |                                                                      |                         |  |             |  |  |  |
| UNLESS OTHERWISE SPECIFIED                   |                      |             |                                                                                       |                                                                                                 |  |  |                                                                      |                         |  |             |  |  |  |

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.





The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant & per IEC 61249-2-21 for Halogen-Free compliant.

| REVISIONS |         |                                                                                                |            |         |
|-----------|---------|------------------------------------------------------------------------------------------------|------------|---------|
| SYM       | ECN No. | DESCRIPTION                                                                                    | DATE       | BY      |
| AX22      | NA      | ADDED COMPONENT KEEP OUT AREA LIMIT HEIGHT                                                     | 10/31/2019 | JOAN LU |
| AX23      | NA      | UPDATED QTY OF PACKAGE                                                                         | 12/17/2019 | JOAN LU |
| AX24      | NA      | 1.CORRECT DIM J IN TABLE FOR G42VXXXXXHR<br>2.REVISED LATCH HOLE DIMENSION FROM 1.10 TO 1.15MM | 09/02/2020 | JOAN LU |
| AX25      | NA      | RECOMMENDED AIC MATING CARD CHAMFER CHANGE FROM C0.75 TO C0.3                                  | 02/02/2021 | JOAN LU |
| AX26      | NA      | ADDED NOTE ITEM 5                                                                              | 03/02/2021 | JOAN LU |





G42VX1XXXHR



G42VX5XXXHR









G42VX2XXXHR



| TOLERANCE                                    |  | DRAWN    | APPROVALS   | DATE         | TITLE                                                                                  |       |    | Amphenol®<br><br>Amphenol Corporation<br>Amphenol Taiwan Corporation |        |          |             |      |      |
|----------------------------------------------|--|----------|-------------|--------------|----------------------------------------------------------------------------------------|-------|----|----------------------------------------------------------------------|--------|----------|-------------|------|------|
| X.<br>X.X ±0.30<br>X.XX ±0.20<br>X.XXX ±0.10 |  | DESIGNED | Joan Lu     | 03/02/2021   | MINI COOL EDGE 10<br>INTEGRATED CONNECTOR<br>0.6 PITCH, VERTICAL<br>STANDARD, SMT TYPE |       |    |                                                                      |        |          |             |      |      |
|                                              |  | CHECKED  | Sondra Sang | 03/02/2021   |                                                                                        |       |    |                                                                      |        |          |             |      |      |
| ANGULAR ±2°                                  |  | APPROVED | Hank Hsu    | 03/02/2021   |   | UNIT  | mm | SIZE                                                                 | A3     | PART No. | G42VXXXXXHR |      |      |
| UNLESS OTHERWISE SPECIFIED                   |  | DWG TYPE | CUST DWG    | PROJECT CODE | T631                                                                                   | SCALE | NA | SHEET                                                                | 2 OF 8 | DWG No.  | G42VXXXXXHR | REV. | AX26 |

The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant & per IEC 61249-2-21 for Halogen-Free compliant.

| REVISIONS |         |                                                                                               |            |         |  |
|-----------|---------|-----------------------------------------------------------------------------------------------|------------|---------|--|
| SYM       | ECN No. | DESCRIPTION                                                                                   | DATE       | BY      |  |
| AX22      | NA      | ADDED COMPONENT KEEP OUT AREA LIMIT HEIGHT                                                    | 10/31/2019 | JOAN LU |  |
| AX23      | NA      | UPDATED QTY OF PACKAGE                                                                        | 12/17/2019 | JOAN LU |  |
| AX24      | NA      | 1.CORRECT DIM J IN TABLE FOR G42VXXXXXX<br>2.REVISED LATCH HOLE DIMENSION FROM 1.10 TO 1.15MM | 09/02/2020 | JOAN LU |  |
| AX25      | NA      | RECOMMENDED AIC MATING CARD CHAMFER CHANGE FROM 0.75 TO 0.3                                   | 02/02/2021 | JOAN LU |  |
| AX26      | NA      | ADDED NOTE ITEM 5                                                                             | 03/02/2021 | JOAN LU |  |



| PART NUMBER  | POS. (N) | DIM. B1 | DIM. B2 | DIM. C | DIM. D1 | DIM. D2 | DIM. E | DIM. F | DIM. G | DIM. H1 | DIM. H2 | DIM. J |
|--------------|----------|---------|---------|--------|---------|---------|--------|--------|--------|---------|---------|--------|
| G42VX4XXXXHR | 124      | 22.48   | 15.28   | 42.00  | 21.60   | 14.40   | 40.50  | 42.15  | 41.15  | 18.90   | 4.50    | 23.85  |
| G42VX6XXXXHR | 148      | 22.48   | 22.48   | 49.20  | 21.60   | 21.60   | 47.70  | 49.35  | 48.35  | 22.50   | 0.90    | 23.85  |



|                                                       |                 |            |              |                                                                                                 |       |    |                                                                      |        |          |             |      |     |
|-------------------------------------------------------|-----------------|------------|--------------|-------------------------------------------------------------------------------------------------|-------|----|----------------------------------------------------------------------|--------|----------|-------------|------|-----|
| TOLERANCE                                             | DRAWN APPROVALS |            | DATE         | TITLE<br>MINI COOL EDGE 10<br>INTEGRATED CONNECTOR<br>0.6 PITCH, VERTICAL<br>STANDARD. SMT TYPE |       |    | Amphenol®<br><br>Amphenol Corporation<br>Amphenol Taiwan Corporation |        |          |             |      |     |
| X.<br>X.X     ±0.30<br>X.XX    ±0.20<br>X.XXX   ±0.10 | DESIGNED        | Joan Lu    | 03/02/2021   |                                                                                                 |       |    |                                                                      |        |          |             |      |     |
| CHECKED                                               | Sondra Sang     | 03/02/2021 |              |                                                                                                 |       |    |                                                                      |        |          |             |      |     |
| APPROVED                                              | Hank Hsu        | 03/02/2021 |              |                                                                                                 |       |    |                                                                      |        |          |             |      |     |
| ANGULAR   ±°                                          |                 |            |              |            | UNIT  | mm | SIZE                                                                 | A3     | PART No. | G42VXXXXXHR |      |     |
| UNLESS OTHERWISE SPECIFIED                            | DWG TYPE        | CUST DWG   | PROJECT CODE | T631                                                                                            | SCALE | NA | SHEET                                                                | 3 OF 8 | DWG No.  | G42VXXXXXHR | REV. | AX2 |

The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant & per IEC 61249-2-21 for Halogen-Free compliant.

|                                                                                              |              |           |
|----------------------------------------------------------------------------------------------|--------------|-----------|
| <h1>Amphenol®</h1> <p><b>Amphenol Corporation</b><br/><b>Amphenol Taiwan Corporation</b></p> |              |           |
| PART NO.                                                                                     | G42VXXXXXXHR |           |
| DWG. NO.                                                                                     | G42VXXXXXXHR | REV. AX26 |

This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant & per IEC 61249-2-21 for Halogen-Free compliant.

| REVISIONS |         |                                                                                                 |            |         |
|-----------|---------|-------------------------------------------------------------------------------------------------|------------|---------|
| SYM       | ECN No. | DESCRIPTION                                                                                     | DATE       | BY      |
| AX22      | NA      | ADDED COMPONENT KEEP OUT AREA LIMIT HEIGHT                                                      | 10/31/2019 | JOAN LU |
| AX23      | NA      | UPDATED QTY OF PACKAGE                                                                          | 12/17/2019 | JOAN LU |
| AX24      | NA      | 1.CORRECT DIM J IN TABLE FOR G42VX6XXXXHR<br>2.REVISED LATCH HOLE DIMENSION FROM 1.10 TO 1.15MM | 09/02/2020 | JOAN LU |
| AX25      | NA      | RECOMMENDED AIC MATING CARD CHAMFER CHANGE FROM 0.75 TO 0.3                                     | 02/02/2021 | JOAN LU |
| AX26      | NA      | ADDED NOTE ITEM 5                                                                               | 03/02/2021 | JOAN LU |

| PART NUMBER  | POS. (N) | DIM. P | DIM. Q |
|--------------|----------|--------|--------|
| G42VX1XXXXHR | 38       | 15.00  | 15.15  |
| G42VX5XXXXHR | 50       | 18.60  | 18.75  |
| G42VX2XXXXHR | 74       | 25.80  | 25.95  |

COMPONENTS KEEP OUT AREA  
LIMITATION HEIGHT: 0mm


COMPONENTS KEEP OUT AREA

COMPONENTS KEEP OUT AREA

| PART NUMBER  | POS. (N) | DIM. P | DIM.Q |
|--------------|----------|--------|-------|
| G42VX4XXXXHR | 124      | 42.75  | 44.75 |
| G42VX6XXXXHR | 148      | 49.95  | 51.95 |



| TOLERANCE                                    |  | DRAWN    | APPROVALS   | DATE         | TITLE                                                                                  |                                                                                       |             | Amphenol®                                           |          |             |              |
|----------------------------------------------|--|----------|-------------|--------------|----------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------|-----------------------------------------------------|----------|-------------|--------------|
| X.<br>X.X ±0.30<br>X.XX ±0.20<br>X.XXX ±0.10 |  | DESIGNED | Joan Lu     | 03/02/2021   | MINI COOL EDGE 10<br>INTEGRATED CONNECTOR<br>0.6 PITCH, VERTICAL<br>STANDARD, SMT TYPE |                                                                                       |             | Amphenol Corporation<br>Amphenol Taiwan Corporation |          |             |              |
|                                              |  | CHECKED  | Sondra Sang | 03/02/2021   |                                                                                        |                                                                                       |             |                                                     |          |             |              |
|                                              |  | APPROVED | Hank Hsu    | 03/02/2021   |                                                                                        |                                                                                       |             |                                                     |          |             |              |
| ANGULAR ±2°                                  |  | DWG TYPE | CUST DWG    | PROJECT CODE | T631                                                                                   |  | UNIT<br>mm  | SIZE<br>A3                                          | PART No. | G42VXXXXXHR |              |
| UNLESS OTHERWISE SPECIFIED                   |  |          |             |              |                                                                                        |  | SCALE<br>NA | SHEET<br>5 OF 8                                     | DWG No.  | G42VXXXXXHR | REV.<br>AX26 |




This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant & per IEC 61249-2-21 for Halogen-Free compliant.

| REVISIONS |         |                                                                                                 |            |         |
|-----------|---------|-------------------------------------------------------------------------------------------------|------------|---------|
| SYM       | ECN No. | DESCRIPTION                                                                                     | DATE       | BY      |
| AX22      | NA      | ADDED COMPONENT KEEP OUT AREA LIMIT HEIGHT                                                      | 10/31/2019 | JOAN LU |
| AX23      | NA      | UPDATED QTY OF PACKAGE                                                                          | 12/17/2019 | JOAN LU |
| AX24      | NA      | 1.CORRECT DIM J IN TABLE FOR G42VX0XXXXHR<br>2.REVISED LATCH HOLE DIMENSION FROM 1.10 TO 1.15MM | 09/02/2020 | JOAN LU |
| AX25      | NA      | RECOMMENDED AIC MATING CARD CHAMFER CHANGE FROM C0.75 TO C0.3                                   | 02/02/2021 | JOAN LU |
| AX26      | NA      | ADDED NOTE ITEM 5                                                                               | 03/02/2021 | JOAN LU |


RECOMMENDED AIC MATING CARD DIMENSIONS



| PART NUMBER  | POS. (N) | DIM. B1 | DIM. D |
|--------------|----------|---------|--------|
| G42VX1XXXXHR | 38       | 11.6    | 10.80  |
| G42VX5XXXXHR | 50       | 15.2    | 14.40  |
| G42VX2XXXXHR | 74       | 22.4    | 21.6   |



| TOLERANCE                  |                         | DRAWN    | APPROVALS   | DATE         | TITLE                                                                                  |             |                 | Amphenol®                                           |             |  |      |      |
|----------------------------|-------------------------|----------|-------------|--------------|----------------------------------------------------------------------------------------|-------------|-----------------|-----------------------------------------------------|-------------|--|------|------|
| X.<br>X.X<br>X.XX<br>X.XXX | ±0.30<br>±0.20<br>±0.10 | DESIGNED | Joan Lu     | 03/02/2021   | MINI COOL EDGE 10<br>INTEGRATED CONNECTOR<br>0.6 PITCH, VERTICAL<br>STANDARD, SMT TYPE |             |                 | Amphenol Corporation<br>Amphenol Taiwan Corporation |             |  |      |      |
|                            |                         | CHECKED  | Sondra Sang | 03/02/2021   |                                                                                        |             |                 |                                                     |             |  |      |      |
|                            |                         | APPROVED | Hank Hsu    | 03/02/2021   |                                                                                        |             |                 |                                                     |             |  |      |      |
| ANGULAR                    | ±2°                     |          |             |              |   | UNIT<br>mm  | SIZE<br>A3      | PART No.                                            | G42VXXXXXHR |  |      |      |
| UNLESS OTHERWISE SPECIFIED |                         | DWG TYPE | CUST DWG    | PROJECT CODE | T631                                                                                   | SCALE<br>NA | SHEET<br>6 OF 8 | DWG No.                                             | G42VXXXXXHR |  | REV. | AX26 |





This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant & per IEC 61249-2-21 for Halogen-Free compliant.

| REVISIONS |         |                                                                                                 |            |         |
|-----------|---------|-------------------------------------------------------------------------------------------------|------------|---------|
| SYM       | ECN No. | DESCRIPTION                                                                                     | DATE       | BY      |
| AX22      | NA      | ADDED COMPONENT KEEP OUT AREA LIMIT HEIGHT                                                      | 10/31/2019 | JOAN LU |
| AX23      | NA      | UPDATED QTY OF PACKAGE                                                                          | 12/17/2019 | JOAN LU |
| AX24      | NA      | 1.CORRECT DIM J IN TABLE FOR G42VX6XXXXHR<br>2.REVISED LATCH HOLE DIMENSION FROM 1.10 TO 1.15MM | 09/02/2020 | JOAN LU |
| AX25      | NA      | RECOMMENDED AIC MATING CARD CHAMFER CHANGE FROM C0.75 TO C0.3                                   | 02/02/2021 | JOAN LU |
| AX26      | NA      | ADDED NOTE ITEM 5                                                                               | 03/02/2021 | JOAN LU |

RECOMMENDED AIC MATING CARD DIMENSIONS



| PART NUMBER  | POS. (N) | DIM. D1 | DIM. D2 | DIM. H1 | DIM. H2 | DIM. T | DIM. T1 | DIM. T2 |
|--------------|----------|---------|---------|---------|---------|--------|---------|---------|
| G42VX4XXXXHR | 124      | 21.60   | 14.40   | 18.90   | 4.50    | 38.6   | 22.4    | 15.2    |
| G42VX6XXXXHR | 148      | 21.60   | 21.60   | 22.50   | 0.90    | 45.8   | 22.4    | 22.4    |




| TOLERANCE                  | DRAWN    | APPROVALS   | DATE         | TITLE                |         | Amphenol®                   |         |           |
|----------------------------|----------|-------------|--------------|----------------------|---------|-----------------------------|---------|-----------|
| X. ±0.30                   | DESIGNED | Joan Lu     | 03/02/2021   | MINI COOL EDGE IO    |         | Amphenol Corporation        |         |           |
| X.X ±0.20                  | CHECKED  | Sondra Sang | 03/02/2021   | INTEGRATED CONNECTOR |         | Amphenol Taiwan Corporation |         |           |
| X.XX ±0.10                 | APPROVED | Hank Hsu    | 03/02/2021   | 0.6 PITCH, VERTICAL  |         | PART No. G42VXXXXXHR        |         |           |
| ANGULAR ±2°                | DWG TYPE | CUST DWG    | PROJECT CODE | T631                 |         | DWG No. G42VXXXXXHR         |         |           |
| UNLESS OTHERWISE SPECIFIED |          |             |              |                      | UNIT mm |                             | SIZE A3 | REV. AX26 |
|                            |          |             |              | SCALE NA             |         | SHEET 7 OF 8                |         |           |





This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant & per IEC 61249-2-21 for Halogen-Free compliant.

| REVISIONS |         |                                                                                                 |            |         |
|-----------|---------|-------------------------------------------------------------------------------------------------|------------|---------|
| SYM       | ECN No. | DESCRIPTION                                                                                     | DATE       | BY      |
| AX22      | NA      | ADDED COMPONENT KEEP OUT AREA LIMIT HEIGHT                                                      | 10/31/2019 | JOAN LU |
| AX23      | NA      | UPDATED QTY OF PACKAGE                                                                          | 12/17/2019 | JOAN LU |
| AX24      | NA      | 1.CORRECT DIM J IN TABLE FOR G42VX6XXXXHR<br>2.REVISED LATCH HOLE DIMENSION FROM 1.10 TO 1.15MM | 09/02/2020 | JOAN LU |
| AX25      | NA      | RECOMMENDED AIC MATING CARD CHAMFER CHANGE FROM 0.75 TO 0.3                                     | 02/02/2021 | JOAN LU |
| AX26      | NA      | ADDED NOTE ITEM 5                                                                               | 03/02/2021 | JOAN LU |



| PART NUMBER  | POS. (N) | DIM. J | DIM. K    | DIM. L   | REEL (QTY) | CARTON (PCS) |
|--------------|----------|--------|-----------|----------|------------|--------------|
| G42VX1XXXXHR | 38       | (21.5) | 28.4±0.1  | 32.0±0.3 | 7          | 1400         |
| G42VX5XXXXHR | 50       | (27.7) | 40.4±0.1  | 44.0±0.3 | 5          | 1000         |
| G42VX2XXXXHR | 74       | (34.0) | 52.4±0.1  | 56.0±0.3 | 4          | 800          |
| G42VX4XXXXHR | 124      | (39.5) | 68.40±0.1 | 72.0±0.3 | 3          | 600          |
| G42VX6XXXXHR | 148      | (57.9) | 68.40±0.1 | 72.0±0.3 | 3          | 600          |



NOTE 1:

1.MATERIAL:  
CARRIER TAPE: POLYSTYRENE, BLACK  
COVER TAPE: TRANSPARENT POLYSTYRENE  
REEL: POLYSTYRENE, BLACK

2.ALL TAPE AND REEL SPECIFICATION FOLLOW EIA-481 STANDARD.

3.THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS MATERIALS PER DERCTIVE 2011/65/EU & 2015/863/EU FOR RoHS AND PER IEC 61249-2-21 FOR HALOGEN FREE.



NOTE 2:

1. CARTON SIZE  
340L X 340W X265H

2. PREFER TO AMTA LABELING STANDARD.

3. CARTON CLOSURES MUST BE SEALES WITH TAPE.

| TOLERANCE                                    | DRAWN    | APPROVALS   | DATE         | TITLE                                     |  | UNIT    |  | SIZE        | PART No.    |
|----------------------------------------------|----------|-------------|--------------|-------------------------------------------|--|---------|--|-------------|-------------|
| X.<br>X.X ±0.30<br>X.XX ±0.20<br>X.XXX ±0.10 | DESIGNED | Joan Lu     | 03/02/2021   | MINI COOL EDGE 10<br>INTEGRATED CONNECTOR |  | mm      |  | A3          | G42VXXXXXHR |
| ANGULAR ±2°                                  | CHECKED  | Sondra Sang | 03/02/2021   | 0.6 PITCH, VERTICAL<br>STANDARD. SMT TYPE |  | SCALE   |  | 8 OF 8      | REV. AX26   |
| UNLESS OTHERWISE SPECIFIED                   | DWG TYPE | CUST DWG    | PROJECT CODE | T631                                      |  | DWG No. |  | G42VXXXXXHR |             |