




1. MATERIALS AND FINISHES:
BODY & C NUT - BERYLLIUM COPPER, GOLD PLATING
CONTACT - BERYLLIUM COPPER, GOLD PLATING
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL, 901-101-15, AND DATE CODE"

5. SHOWS CABLE ENTRY DIMENSION



RECOMMENDED CABLE STRIPPING DIMENSION

901-101-15		REVISIONS				
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR	
THIRD ANGLE PROJ. 	--	RELEASE TO MFG.	--	--	--	
	W	REDRAWN IN PRO-E, ADDED SHT 2	8/10/09	47526	NMV	



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1°			MATERIAL		DRAWN NISCHIT MV		DATE 12-Jun-09		TITLE SMA CONNECTOR CRIMP TYPE PLUG FOR RG400/U & RG 142B/U CABLE			Amphenol RF Danbury, CT, USA Tainan, Taiwan Shenzhen, China www.amphenolrf.com		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.					ENGINEER RPA		DATE 6/29/71							
			REFERENCE			APPROVED K. CAPOZZI		DATE 8/10/09						
CAD FILE 1:SMA/ 901-101-15						CODE ID 74868		DWG SIZE B	DRAWING NO. 901-101-15			REV W		