Specification

Drawing No.	TNY1T-H1-MEE01-05 [1/8]
Issued Date.	16-Jul-26

TO:

Note : In case of specification change, KYOCERA Part Number also will be changed.

Product Name	Crystal Oscillator
Product Model	————————
Frequency	30 MHz
Customer Part Number	---
Customer Specification Number	————————
KYOCERA Part Number	MC2016K30.0000C16ESH
Remarks RoHS Compliant / MSL 1 / AEC-Q200 Certified	

Customer Acceptance

Accept Signature	Accept Date	
	Department	
	Person in charge	

Seller
KYOCERA Corporation
Corporate Electronic Components Group
Electronic Components Sales Division
6 Takeda Tobadono-cho, Fushimi-ku, Kyoto
612-8501 Japan
TEL. No. 075-604-3500
FAX. No. 075-604-3501

Manufacturer
KYOCERA Corporation
Corporate Electronic Components Group
Electronic Devices Division
Yamagata higashine Plant
5850, Higashine-koh, Higashine-shi, Yamagata 999-3701 Japan
TEL. No. 0237-43-5611
FAX. No. 0237-43-5615

Design Department	Quality Assurance	Approved by	Checked by	Issued by
Oscillator Application Engineering Section Electronic Devices Division				

Downloaded from Arrow.com.

Revision History

Rev. No.	Description of revise	Date	Approved by	Checked by	Issued by
00	**First Edition**	**16-Jul-26**			

Downloaded from Arrow.com.

1. Scope

This specification shall be defined of the Clock Oscillator for the integrated circuits (ICs).

2. Customer Part Number

---

3. KYOCERA Part Number

MC2016K30.0000C16ESH

4. Electrical Characteristics

4-1. Absolute Maximum Rating

Item	Symbol	Rated Value	Units
Power Supply Voltage	V_{CC}	-0.3 to +4.0	V
Input Voltage	V_{IN}	-0.3 to V_{CC} +0.3	V
Storage Temperature	T_{STG}	-55 to +125	°C

Note:
If the part is used beyond absolute maximum ratings, it may cause internal destruction. The part should be used under the recommended operating conditions the reliability of this part may be damaged if those conditions are exceeded.

4-2. Recommended Operating Conditions

Item	Symbol	Min	Typ	Max	Units	Remarks
Power Supply Voltage	V_{CC}	1.6	3.3	3.63	V	
Input Voltage	V_{IN}	0	---	V_{CC}	V	
Operating Temperature	T_{OPR}	-40	25	+105	°C	

4-3. Electrical Characteristics

Item	Symbol	Min	Typ	Max	Units	Remarks
Output Frequency	F_O	--	30	--	MHz	
Frequency Tolerance*	F_{tol}	-50	--	+50	ppm	
Current Consumption (Loaded/ 1.6≤V_{CC}≤2.25V)	I_{CC}	--	--	3.5	mA	
Current Consumption (Loaded/ 2.25<V_{CC}≤2.8V)		--	--	4.5		
Current Consumption (Loaded/ 2.8<V_{CC}≤3.63V)		--	--	5		
Standby Current	I_{ST}	--	--	5	µA	
Symmetry (Duty Ratio)	SYM	45	50	55	%	@50% Vcc
Rise Time/ Fall Time (10% V_{CC} to 90% V_{CC})	Tr/ Tf	--	--	6	ns	1.6≤V_{CC}≤2.25V
		--	--	5		2.25<V_{CC}≤2.8V
		--	--	4.5		2.8<V_{CC}≤3.63V
Output Voltage-"L"	V_{OL}	---	---	10% V_{CC}	V	I_{OL}=4mA
Output Voltage-"H"	V_{OH}	90% V_{CC}	---	---	V	I_{OH}=-4mA
Output Load	CL	---	---	15	pF	CMOS
Input Voltage-"L"	V_{IL}	---	---	30% V_{CC}	V	
Input Voltage-"H"	V_{IH}	70% V_{CC}	---	---	V	
Output Disable Time	t_{dis}	---	---	200	ns	
Output Enable Time	t_{ena}	---	---	2	ms	
Start-up Time	t_{sta}	---	---	2	ms	@Minimum operating voltage to be 0sec
1 Sigma Jitter**	J_{Sigma}	---	---	5	ps	
Peak to Peak Jitter**	J_{PK-PK}	---	---	50	ps	
Phase Jitter	---	---	---	1	ps	BW:12kHz to 20MHz

Note: All electrical characteristics have defined on the maximum loaded and recommended operating conditions.
* Include initial tolerance, operating temperature range, rated power supply voltage change, load change, aging (1year @+25°C), shock and vibration
**Based on Time Interval Analyzer "Wavecrest SIA-3600C".


Table 1

Downloaded from Arrow.com.

4-4. Measurement Condition
The reference temperature shall be +25±2ºC. The measurement shall be performed at the temperature range of +5 ºC to +35 ºC unless otherwise the result is doubtful.

4-5. Measurement Circuit
The electrical characteristics shall be measured by test circuit "Fig. 1". Also jitter shall be measured by test circuit "Fig. 3".

4-6. Clock Timing Chart
The clock timing chart is "Fig. 2".



Note: CL includes probe and test fixture capacitance

Fig.1 Test Circuits





Fig.2 Clock Timing Chart (C-MOS Output)




<Measurement Conditions>


- Time Interval Analyzer
  - WaveCrest SIA-3600C
- DTS timer calibration
  - Over 30 minutes warm-up
  - Extend 30 minutes calibration
- Jitter histogram conditions (Tail-fit)
  - More than 50,000cyc Hits
  - Bit Error Ratio (BER) –12 (14sigma)

Fig.3 Jitter Test Circuits

5. Dimensions and Marking



Plating Ni+Au
Tolerance:+/-0.2
Unit:(mm)



Output Frequency

The output frequency is three-digit without a decimal point. The frequency greater than the number of digits have rounded down.

(E.g. 14.31818MHz ➔ "14.3")

Manufacturing Date Code

Year	Code	Year	Code
2020	W	2031	L
2021	A	2032	M
2022	B	2033	N
2023	C	2034	P
2024	D	2035	Q
2025	E	2036	R
2026	F	2037	S
2027	G	2038	T
2028	H	2039	V
2029	J	2040	W
2030	K	2041	A

It repeats from A in 2041 and after wards.

Month	Code
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	A
11	B
12	C

Day	Code	Day	Code	Day	Code
1	1	11	B	21	M
2	2	12	C	22	N
3	3	13	D	23	P
4	4	14	E	24	Q
5	5	15	F	25	R
6	6	16	G	26	S
7	7	17	H	27	T
8	8	18	J	28	V
9	9	19	K	29	W
10	A	20	L	30	X
				31	Y

e.g. :"P4A" means "Apr-10-2034"

Table 2

Pad arrangement	
1	Stand-by Function
2	Case GND
3	Output
4	V_{CC}

Stand-by Function	
Pad1	Pad3 (Output)
OPEN	Active
"H" Level	Active
"L" Level	High Z (No-Oscillation)

Downloaded from Arrow.com.

6. Parts Numbering Guide

MC2016K 30.0000 C 1 6 E SH
A B C D E F G



A. Series (SMD Oscillator)
B. Output Frequency
C. Output
C: C-MOS
D. Supply Voltage
1: 1.8V/ 2.5V/ 3.3V Compatible
E. Frequency Tolerance*
6: ±50ppm
F: Symmetry (Duty Ratio) and Stand-by Function
E: Symmetry: 45% to 55% with Stand-by Function
G. Suffix for Individual Requirements
SH : for Automotive

Packing (Tape & Reel 2,000pcs/Reel)
*Over All Conditions:
Include initial tolerance, operating temperature range, rated power supply voltage change, load change, aging (1year @+25°C), shock and vibration

7. Environmental Characteristics (Based on AEC-Q200 Rev. D)

AEC-Q200 No	Items	Conditions	Reference	Criteria of Acceptance	Sample Size [PCS]
3	High Temperature Exposure (Storage)	+125°C 1000 hrs. Unpowered.	MIL-STD-202 Method 108	Satisfy Electrical Characteristics.	77
4	Temperature Cycling	1000cycles (-55 to +125°C)	JESD22 Method JA-104	Satisfy Electrical Characteristics.	77
6	Moisture Resistance	+25°C, +65°C 90%RH 10cycles 24 hrs/1cycle. Unpowered. Steps 7a & 7b not required.	MIL-STD-202 Method 106	Satisfy Electrical Characteristics. Clause 13 shall be also satisfied.	77
7	Biased Humidity	+85°C, 85%RH, 1000 hrs. VCC=3.63V, CL=15pF	MIL-STD-202 Method 103	Satisfy Electrical Characteristics.	77
8	Operational Life	+125°C, 1000 hrs. VCC=3.63V, CL=15pF	MIL-STD-202 Method 108	Satisfy Electrical Characteristics.	77
9	External Visual	Magnification 10x	MIL-STD-883 Method 2009	Thing that abnormality is not found in externals. (Inspect device construction, marking and workmanship. Electrical Test not required.)	30
10	Physical Dimension	-	JESD22 Method JB-100	Satisfy Approval Sheet	30
12	Resistance to Solvents	Magnification 10x	MIL-STD-202 Method 215	Thing that abnormality is not found in externals.	5
13	Mechanical Shock	100G/6ms/Half-sine Velocity change 12.3 (Vi)ft/sec	MIL-STD-202 Method 213	Satisfy Electrical Characteristics.	30
14	Vibration	10 to 2000Hz. 5g's for 20 minutes 12 cycles each of 3 orientations.	MIL-STD-202 Method 204	Satisfy Electrical Characteristics.	30
15	Resistance to Soldering Heat	Soaking:+260±5°C, 10±1sec	MIL-STD-202 Method 210	Satisfy Electrical Characteristics.	30
16	Thermal Shock	-55°C/+125°C. 300Cycles, Max. transfer time 20 sec. Dwell time 5 min. Air-Air.	MIL-STD-202 Method 107	Satisfy Electrical Characteristics.	30


Downloaded from Arrow.com.

AEC-Q200 No	Items	Conditions	Reference	Criteria of Acceptance	Sample Size [PCS]
17	ESD	Human Body Model: 100pF/1500ohm/500~2000V 5 pulses	AEC-Q200-002	Satisfy Electrical Characteristics.	15
18	Solderability	8 hrs. steam age +215°C solder temperature 5 second dwell	J-STD-002	Dipped potion: Minimum 95% coverage	15
19	Electrical Characterization	-	Approval Sheet	Satisfy Approval Sheet	30 x 3Lot
21	Board Flex	It pressurizes in the direction of the arrow, it pressurizes at the speed of 2mm in bend width about 0.5mm/sec, and it maintains it for 60 seconds. 	AEC-Q200-005	Satisfy Electrical Characteristics. Without looseness or crack etc.	30
22	Terminal Strength (SMD)	The static load of 1.8Kg is added in the direction of the arrow and it maintains it in the prime fields of parts for 60 sec with a scratch treatment device of R0.5. 	AEC-Q200-006	Satisfy Electrical Characteristics. Without looseness or crack etc.	30

After each testing, the parts shall be subjected to standard atmospheric conditions more than 2 hours.

Table 3

8. Recommended Land pattern and Soldering Guide




Unit: (mm)

Note:

Since the part doesn't have Bypass Capacitor between V_{cc} and GND, Please mount high frequency type capacitor 0.01μF to the nearest position of oscillator.

Fig.4 Land pattern




Available Reflow times: Maximum twice

Fig.5 Reflow profile (Lead Free Available)

Downloaded from Arrow.com.


9. Taping Specifications



Unit: (mm)

Symbol	A_0	B_0	W	F	E
Dimensions	1.9±0.2	2.3±0.2	8.0±0.2	3.5±0.05	1.75±0.1
Symbol	P_1	P_2	P_0	D_0	T
Dimensions	4.0±0.1	2.0±0.05	4.0±0.1	1.5+0.1/-0	0.25±0.1
Symbol	K	D_1			
Dimensions	0.9±0.1	1.1±0.1			

Fig.6 Emboss Carrier Tape




Unit: (mm)

Symbol	A	N	W_1
Dimensions	180 +0/-1.5	60+1/–0	9.0+0.3/-0
Symbol	W_2	C	D
Dimensions	11.4±1.0	13.0±0.2	21.0±0.8
Symbol	E		
Dimensions	2.0±0.5		

Fig.7 Reel

9-1. Taping Quantities
- The taping of per reel shall be packed 2,000 pcs.
- The parts shall be contained continuously in the pocket.

9-2. Leader and Blank Pockets
- The package shall be consisted of leader, blank pockets and loaded pocket as follows “Fig. 8”.
- The power of peeling strength between top tape and carrier tape shall be 0.1N(10gf) to 1.0N(100gf) as follows “Fig. 9”.



A) Leader
B) Blank Pocket (40mm to 320mm)
A+B: 400mm to 560mm
C) Load Pocket
D) Blank Pocket (160mm minimum)

Fig.8 Packing Method




Fig.9 Peeling Strength

9-3. Reel Label
The reel label shall be consisted as below. (Based on EIAJ C-3 format)
A) Customer Part Number
B) Lot No.
C) Quantities
D) Shipping Date
E) Vender Name

9-4. Exterior Package Label
The oscillator shall be packed properly to avoid defect in transportation. The exterior package label shall be consisted as below.
A) Name of Customer
B) P/O No.
C) Customer Part Number
D) Lot No.
E) Quantities
F) Shipping Date
G) Vender Name

Downloaded from Arrow.com.

10. The agreement of this specifications

In case there is any obscure point or doubt concerning the contents of the specification, it shall be settled through consultation of both parties.

11. Quality guarantee

In case when Kyocera Corporation rooted failure occurred within 1year after its delivery, substitute product will be arranged based on discussion. Quality guarantee of product after 1year of its delivery is waivered.

12. Remarks on Usages

A) Storage Conditions
The parts shall be stored in temperature range of -5 to +40°C, humidity 40 to 60% RH, and avoid direct sunlight. Then the parts shall be used within 6 months.

B) Handling Conditions
Although the part has protection circuit against static electricity, when excess static electricity is applied, the inside IC may get damaged.
Before mounting on the PCB, please make sure the direction of the part is correct. Otherwise the part of temperature will increase. And also the part will have some damages.
Please do not use the parts under the unfavorable condition such as beyond specified range in this specification.
Please do not use the parts under the condition, in the water or in the salt water also environment of dew or harmful gas.

Please make sure the condition of pick and place following pick up nozzle guideline.

Picking Method: Case of Head Unit 1.6 x 1.2mm (Inside Diameter)

The proper condition of pick and place will be different each equipment. Therefore, please check before testing.

C) Rework Condition
Please do not pick up Head Unit. We can't guaranty electrical performance and reliability.

D) Soldering Conditions
This product can respond to the general Pb-free reflow profile. The wave soldering cannot be supported.

E) Soldering in Mounting
In case of Solder paste and conductive glue contact product lid or product side face exception for product terminal it's possible to influence product characteristics.
Please be careful above contents.

F) Washing Conditions
Ultra sonic cleaning is available. However there is a possibility that Crystal in the part may cause damaged under certain condition. Therefore please test before using.
After washing, please dry the parts completely. Otherwise water drops between the parts and PCB may cause migration.

G) This product is not intended for use in applications that require particularly high levels of quality or reliability, or in devices or systems where the absence of fail-safe circuits or similar safeguards could result in failure or malfunction that directly threatens human life, causes personal injury, or is expected to have a significant impact on property or other assets.
Should this product nevertheless be used in such applications, our company shall bear no responsibility whatsoever for any damages or losses arising from such use.

In case of using this part without above precaution, Kyocera is unable to guarantee the specific characteristics.

KYOCERA Corporation

Downloaded from Arrow.com.