

## SPECIFICATIONS

| PARAMETER                            | VALUE                   |
|--------------------------------------|-------------------------|
| NOMINAL FREQUENCY                    | 50.000 MHz              |
| MODE OF OSCILLATION                  | FUNDAMENTAL             |
| FREQUENCY TOLERANCE AT 25°C          | ±20 PPM MAXIMUM         |
| FREQUENCY STABILITY OVER TEMPERATURE | ±20 PPM MAXIMUM         |
| OPERATING TEMPERATURE RANGE          | -40°C TO +85°C          |
| STORAGE TEMPERATURE RANGE            | -40°C TO +85°C          |
| AGING                                | ±3 PPM PER YEAR MAXIMUM |
| LOAD CAPACITANCE                     | 10 pF                   |
| EQUIVALENT SERIES RESISTANCE         | 50 Ω MAXIMUM            |
| SHUNT CAPACITANCE                    | 5 pF MAXIMUM            |
| DRIVE LEVEL                          | 100 μW MAXIMUM          |
| INSULATION RESISTANCE                | 500 MΩ MINIMUM          |






Photo is not actual part

## MECHANICAL SPECIFICATION



## CARRIER TAPE DIMENSIONS




NOTE: REFER TO EIA-481 FOR DIMENSIONS

## PACKAGING

178 mm REEL DIAMETER  
8 mm TAPE WIDTH, 4 mm PITCH  
QUANTITY: 3000 PIECES PER REEL  
IN ACCORDANCE WITH EIA-481

## REFLOW PROFILE



| Reflow profile                                 |                               |              |
|------------------------------------------------|-------------------------------|--------------|
| Temperature Min Preheat                        | $T_{SMIN}$                    | 125°C        |
| Temperature Max Preheat                        | $T_{SMAX}$                    | 150°C        |
| Time ( $T_{SMIN}$ to $T_{SMAX}$ )              | $t_s$                         | 30-60 sec.   |
| Temperature                                    | $T_L$                         | 217°C        |
| Peak Temperature                               | $T_P$                         | 260°C        |
| Ramp-up rate                                   | $R_{UP}$                      | 3°C/sec max. |
| Ramp-down rate                                 | $R_{DOWN}$                    | 6°C/sec max. |
| Time within 5°C of Peak Temperature            | $t_p$                         | 10 sec.      |
| Time $t[25^\circ\text{C}]$ to Peak Temperature | $t[25^\circ\text{C}]$ to Peak | 120 sec.     |
| Time                                           | $t_L$                         | 60-150 sec.  |

## ENVIRONMENTAL

| PARAMETER                  | VALUE                     |
|----------------------------|---------------------------|
| MOISTURE SENSITIVITY LEVEL | 1                         |
| RoHS-2                     | 6/6 COMPLIANT & LEAD FREE |
| REACH SVHC                 | COMPLIANT                 |
| HALOGEN-FREE               | COMPLIANT                 |
| ESD CLASSIFICATION LEVEL   | N/A                       |
| TERMINATION FINISH         | Au                        |



## ● MARKING

R50.00

xxKDyw

x – Internal Production ID code

y – Year code

w – Week code

| YEAR CODE |      |
|-----------|------|
| Year      | Code |
| 2011      | 1    |
| 2012      | 2    |
| 2013      | 3    |
| 2014      | 4    |
| 2015      | 5    |
| 2016      | 6    |
| 2017      | 7    |
| 2018      | 8    |
| 2019      | 9    |

| ALPHA WEEK CODE TABLE |      |      |      |      |      |
|-----------------------|------|------|------|------|------|
| Week                  | Code | Week | Code | Week | Code |
| 1                     | a    | 19   | s    | 37   | K    |
| 2                     | b    | 20   | t    | 38   | L    |
| 3                     | c    | 21   | u    | 39   | M    |
| 4                     | d    | 22   | v    | 40   | N    |
| 5                     | e    | 23   | w    | 41   | O    |
| 6                     | f    | 24   | x    | 42   | P    |
| 7                     | g    | 25   | y    | 43   | Q    |
| 8                     | h    | 26   | z    | 44   | R    |
| 9                     | i    | 27   | A    | 45   | S    |
| 10                    | j    | 28   | B    | 46   | T    |
| 11                    | k    | 29   | C    | 47   | U    |
| 12                    | l    | 30   | D    | 48   | V    |
| 13                    | m    | 31   | E    | 49   | W    |
| 14                    | n    | 32   | F    | 50   | X    |
| 15                    | o    | 33   | G    | 51   | Y    |
| 16                    | p    | 34   | H    | 52   | Z    |
| 17                    | q    | 35   | I    |      |      |
| 18                    | r    | 36   | J    |      |      |

## ● APPROVAL

|             |                       |
|-------------|-----------------------|
| DRAWN BY    | KJackson, May 4, 2016 |
| APPROVED BY | KJackson, May 4, 2016 |
| REVISION    | A, Initial Release    |