


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REDRAWN & REVISED PER ECO-17-013201	13SEP2017	RS	DR



1 FOR 2.921[.115] TO 4.318[.170] WIRE INSULATION DIA,
BODY MATERIAL THICKNESS: 0.787±0.051[.031±.002]

2 NOTE DELETED.

3 STAMP AMP 16-14* APPROX AS SHOWN.

1000	LOOSE PIECE	BODY: COPPER (QQ-C-576) TIN PL(MIL-T-10727) SLEEVE: COPPER (QQ-C-576) INSULATION: PVC, COLOR: BLUE	32441
QTY.	PACKAGE TYPE	MATERIAL & FINISH	PART NO

DIMENSIONS: mm [INCHES]	DWN RAVI S	13SEP2017	MATERIAL SEE TABLE	FINISH SEE TABLE
	CHK ROHDE DANIEL F.	13SEP2017		
	APVD ROHDE DANIEL F.	13SEP2017		
	PRODUCT SPEC —		NAME WIRE TERMINAL, P.I.D.G. RING TONGUE, WIRE SIZE:16-14	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.127[.005] 4 PLC ± — ANGLES ± 5°	APPLICATION SPEC —		SIZE A4	CAGE CODE 00779
	WEIGHT —		DRAWING NO C-32441	RESTRICTED TO —
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
			REV C1	