





REV.	DATE	DESCRIPTION
A	01/30/04	UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .118"

8				UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex N CRIMP PLUG, REVERSE POLARIZED BEIDEN 9913, 9914 BRAND REX H243 + LMR 400 1722102H243RP
7				UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	DRAWN	G.R.S.	
6				TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED		
5				UNLESS OTHERWISE SPECIFIED, DIMENSIONS FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	ISSUED		
4	FERRULE	COPPER	NEXCOTE		SHEET	1 OF 1	
3	CONTACT PIN	PHOS. BRONZE	GOLD				
2	INSULATOR	TEFLON	NATURAL				
1	BODY	BRASS	NEXCOTE				
DESCRIPTION				MATERIAL	FINISH	QTY	
						DO NOT SCALE DRAWING	
						CAD FILE	
						C:/172/172102H243RP.DWG	
						DWG. NO.	
						1722102H243RP.DWG	
						REV.	
						A	
						SIZE	
						A	
						SCALE	
						NA	