NTMFS4931N

MOSFET – Power, Single, N-Channel, SO-8 FL
30 V, 246 A

Features
- Low $R_{DS(on)}$ to Improve Conduction and Overall Efficiency
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Applications
- OR–ing FET, Power Load Switch, Motor Control
- Refer to Application Note AND8195/D for Mounting Information

End Products
- Motor Control, UPS, Fault–Tolerant Power Systems, Hot Swap


MAXIMUM RATINGS (T_J = 25°C unless otherwise stated)

Parameter			Symbol	Value	Unit
Drain–to–Source Voltage			V_{DSS}	30	V
Gate–to–Source Voltage			V_{GS}	±20	V
Continuous Drain Current $R_{\theta JA}$ (Note 1)	Steady State	T_A = 25°C	I_D	40	A
		T_A = 100°C		25	
Power Dissipation $R_{\theta JA}$ (Note 1)		T_A = 25°C	P_D	2.74	W
Continuous Drain Current $R_{\theta JA} \le 10$ s (Note 1)		T_A = 25°C	I_D	77	A
		T_A = 100°C		48	
Power Dissipation $R_{\theta JA} \le 10$ s (Note 1)		T_A = 25°C	P_D	10.2	W
Continuous Drain Current $R_{\theta JA}$ (Note 2)		T_A = 25°C	I_D	23	A
		T_A = 100°C		15	
Power Dissipation $R_{\theta JA}$ (Note 2)		T_A = 25°C	P_D	0.95	W
Continuous Drain Current $R_{\theta JC}$ (Note 1)		T_C = 25°C	I_D	246	A
		T_C =100°C		156	
Power Dissipation $R_{\theta JC}$ (Note 1)		T_C = 25°C	P_D	104	W
Pulsed Drain Current	T_A = 25°C, t_p = 10 μs		I_{DM}	490	A
Operating Junction and Storage Temperature			T_J, T_{STG}	–55 to +150	°C
Source Current (Body Diode)			I_S	100	A
Drain to Source DV/DT			dV/d_t	4.4	V/ns


ON Semiconductor®

www.onsemi.com

$V_{(BR)DSS}$	$R_{DS(ON)}$ MAX	I_D MAX
30 V	1.1 mΩ @ 10 V	246 A
	1.5 mΩ @ 4.5 V	




N–CHANNEL MOSFET



SO–8 FLAT LEAD CASE 488AA STYLE 1

MARKING DIAGRAM



A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

Device	Package	Shipping†
NTMFS4931NT1G	SO–8 FL (Pb–Free)	1500 / Tape & Reel
NTMFS4931NT3G	SO–8 FL (Pb–Free)	5000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

© Semiconductor Components Industries, LLC, 2014

Downloaded from Arrow.com.

MAXIMUM RATINGS (T_J = 25°C unless otherwise stated)

Parameter	Symbol	Value	Unit
Single Pulse Drain−to−Source Avalanche Energy (T_J = 25°C, V_{DD} = 24 V, V_{GS} = 10 V, I_L = 41 A_{pk}, L = 0.3 mH, R_G = 25 Ω)	E_{AS}	252	mJ
Lead Temperature for Soldering Purposes (1/8″ from case for 10 s)	T_L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface−mounted on FR4 board using 1 sq−in pad, 1 oz Cu.
2. Surface−mounted on FR4 board using the minimum recommended pad size.

Downloaded from Arrow.com.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction−to−Case (Drain)	$R_{\theta JC}$	1.2	°C/W
Junction−to−Ambient − Steady State (Note 3)	$R_{\theta JA}$	45.7	
Junction−to−Ambient − Steady State (Note 4)	$R_{\theta JA}$	132	
Junction−to−Ambient − (t ≤ 10 s) (Note 3)	$R_{\theta JA}$	12.3	

3. Surface−mounted on FR4 board using 1 sq−in pad, 1 oz Cu.
4. Surface−mounted on FR4 board using the minimum recommended pad size.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
OFF CHARACTERISTICS							
Drain−to−Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 250 μA		30			V
Drain−to−Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS}/T_J$				18		mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{GS} = 0 V, V_{DS} = 24 V	T_J = 25°C			1.0	μA
			T_J = 125°C			15	
Gate−to−Source Leakage Current	I_{GSS}	V_{DS} = 0 V, V_{GS} = ±20 V				±100	nA
ON CHARACTERISTICS (Note 5)							
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 250 μA		1.2	1.6	2.2	V
Negative Threshold Temperature Coefficient	$V_{GS(TH)}/T_J$				4.0		mV/°C
Drain−to−Source On Resistance	$R_{DS(on)}$	V_{GS} = 10 V	I_D = 30 A		0.85	1.1	mΩ
			I_D = 15 A		0.82		
		V_{GS} = 4.5 V	I_D = 30 A		1.2	1.5	
			I_D = 15 A		1.2		
Forward Transconductance	g_{FS}	V_{DS} = 1.5 V, I_D = 15 A			86		S
CHARGES, CAPACITANCES & GATE RESISTANCE							
Input Capacitance	C_{ISS}	V_{GS} = 0 V, f = 1 MHz, V_{DS} = 15 V			9821		pF
Output Capacitance	C_{OSS}				2720		
Reverse Transfer Capacitance	C_{RSS}				234		
Total Gate Charge	$Q_{G(TOT)}$	V_{GS} = 4.5 V, V_{DS} = 15 V; I_D = 30 A			61.5		nC
Threshold Gate Charge	$Q_{G(TH)}$				14.2		
Gate−to−Source Charge	Q_{GS}				25.2		
Gate−to−Drain Charge	Q_{GD}				15.9		
Total Gate Charge	$Q_{G(TOT)}$	V_{GS} = 10 V, V_{DS} = 15 V; I_D = 30 A			128		nC
SWITCHING CHARACTERISTICS (Note 6)							
Turn−On Delay Time	$t_{d(ON)}$	V_{GS} = 4.5 V, V_{DS} = 15 V, I_D = 15 A, R_G = 3.0 Ω			27		ns
Rise Time	t_r				29		
Turn−Off Delay Time	$t_{d(OFF)}$				36		
Fall Time	t_f				24		

5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
SWITCHING CHARACTERISTICS (Note 6)							
Turn−On Delay Time	$t_{d(ON)}$	V_{GS} = 10 V, V_{DS} = 15 V, I_D = 15 A, R_G = 3.0 Ω			15		ns
Rise Time	t_r				17		
Turn−Off Delay Time	$t_{d(OFF)}$				80		
Fall Time	t_f				22		
DRAIN−SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage	V_{SD}	V_{GS} = 0 V, I_S = 30 A	T_J = 25°C		0.8	1.0	V
			T_J = 125°C		0.62		
Reverse Recovery Time	t_{RR}	V_{GS} = 0 V, dIS/dt = 100 A/μs, I_S = 30 A			64		ns
Charge Time	t_a				33		
Discharge Time	t_b				31		
Reverse Recovery Charge	Q_{RR}				100		nC
PACKAGE PARASITIC VALUES							
Source Inductance	L_S	T_A = 25°C			0.50		nH
Drain Inductance	L_D				0.005		nH
Gate Inductance	L_G				1.84		nH
Gate Resistance	R_G				0.7	1.8	Ω

5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. On−Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On−Resistance vs. Gate−to−Source Voltage




Figure 4. On−Resistance vs. Drain Current and Gate Voltage




Figure 5. On−Resistance Variation with Temperature




Figure 6. Drain−to−Source Leakage Current vs. Voltage

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate−To−Source and Drain−To−Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Avalanche Energy vs. Starting Junction Temperature

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 13. Thermal Response





Figure 14. GFS vs. I_D


Downloaded from Arrow.com.



SCALE 2:1


DFN5 5x6, 1.27P
(SO−8FL)
CASE 488AA
ISSUE N

DATE 25 JUN 2018




NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.

	MILLIMETERS		
DIM	MIN	NOM	MAX
A	0.90	1.00	1.10
A1	0.00	–––	0.05
b	0.33	0.41	0.51
c	0.23	0.28	0.33
D	5.00	5.15	5.30
D1	4.70	4.90	5.10
D2	3.80	4.00	4.20
E	6.00	6.15	6.30
E1	5.70	5.90	6.10
E2	3.45	3.65	3.85
e	1.27 BSC		
G	0.51	0.575	0.71
K	1.20	1.35	1.50
L	0.51	0.575	0.71
L1	0.125 REF		
M	3.00	3.40	3.80
θ	0 °	–––	12 °




GENERIC MARKING DIAGRAM*



XXXXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “ ▪”, may or may not be present. Some products may not follow the Generic Marking.

RECOMMENDED SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

STYLE 1:
PIN 1. SOURCE
2. SOURCE
3. SOURCE
4. GATE
5. DRAIN

STYLE 2:
PIN 1. ANODE
2. ANODE
3. ANODE
4. NO CONNECT
5. CATHODE

*For additional information on our Pb−Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	**98AON14036D**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**DFN5 5x6, 1.27P (SO−8FL)**	**PAGE 1 OF 1**

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.