


QTY	DESCRIPTION	COLOR	MATL	ITEM #
1	USB 2.0 wire: 28AWG*1P + 24*2C + AL/MY + BD + DW + jacket, VW-1, 75C, type CL2	Black	PVC	1
1	Connector: USB 2.0 type A, male		Nickel plated shell, gold plated contacts	2
1	PVC overmold with DataPro logo and strain relief	Black	PVC 30P outer, PE inner	3
1	Connector: USB 2.0 type A female		Nickel plated shell, gold plated contacts	4
1	PVC overmold with DataPro logo and strain relief	Black	PVC 30P outer, PE inner	5
2	Screw, pan-head, UNC #4-40, 5/16" (8mm) thread, 0.3925" (12 mm) length		Nickel-plated	6
2	Knurled nut insert, 4-40 thread		Brass	7

Packed with clear polybag



<div>COMPLIANCES</div> <div>REACH (EC 1907/2006)</div> <div>ROHS (2011/65/EU)</div>	1598-01C 1598-02C 1598-03C 1598-04C 1598-06C 1598-10C 1598-15C	305 610 915 1220 1830 3050 4575	50 50 50 50 100 100 150	UNLESS OTHERWISE SPECIFIED:			<div>DataPro</div> <div>TITLE:</div> <div>USB PANEL-MOUNT TYPE A CABLE</div> <div>SIZE<div>A</div>DWG. NO.<div>1598</div>REV<div>10</div></div> <div>SCALE: 1:1WEIGHT:SHEET 1 OF 1</div>					
				DIMENSIONS ARE mm						DRAWN	NWC	05/01/17
				STANDARD TOL ± 0.3						CHECKED	RDH	05/01/17
										ENG APPR.		
										MFG APPR.		
										Q.A.		
										COMMENTS:		
			R10: Length tolerance for 1598-01C increased to 50mm									
<div>PROPRIETARY AND CONFIDENTIAL</div> <div>THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF DATAPRO INTERNATIONAL, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF DATAPRO INTERNATIONAL, INC. IS PROHIBITED.</div>	P/N	L	T	DO NOT SCALE DRAWING								

5

4

3

2

1