




PIDG

TE Internal #: 8-320619-1
Closed Ring Tongue Terminal, 16 – 14 AWG, #6 / M3.5 Stud, 3.68 mm [.145 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 2050 – 5180 CMA

Stud Size: #6, M3.5

[All PIDG Ring Tongue Terminals \(410\)](#)

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#6, M3.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Product Weight	.826 g
----------------	--------

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight



Terminal Plating Material	Tin
---------------------------	-----

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	17.86 mm[.703 in]
Compatible Insulation Diameter (Max)	4.32 mm[.17 in]
Compatible Insulation Diameter Range	2.92 – 4.31 mm[.115 – .17 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Box & Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free




Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 47807-1 DIES PIDG 16-14 DIE SET	 TE Part # 58423-1 DIE, RBY IS9252	 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 169400 CERTI-LOK FRAME W/O DIES
 TE Part # 47387 DAHT PG PIDG 20-14 ASSY	 TE Part # 59250 T-HEAD PIDG 26-14 ASSY	 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	 TE Part # 539691-2 ERGO DIE R.B.Y
 TE Part # 2063030-1 SDE DIESET, RBY, UL	 TE Part # 169404 CERTI-LOK DIE		

Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)




Hand Crimping Tools(2)



Knife Disconnects(11)



Ring Terminals(589)



Spade Terminals(228)



Special Purpose Terminals(1)




Splices(41)

Customers Also Bought




TE Part #52929-3
PIDG SP SPD 22-16COMM22-18MIL6



TE Part #1-104479-1
SHORT POINT RECP CONT LP




TE Part #165085
PG WIRE PIN 12-10




TE Part #2-215882-6
26 WAY BLACK MK II RECP



TE Part #320552
PIDG R 22-16 COMM 22-18 MIL 10




TE Part #926883-1
UNIVERSAL M-N-L PIN



TE Part #1604197-1
NUT,JAM,7/16-28,PKG QTY 100



TE Part #1-1649341-9
T9CP5A54-120



TE Part #GA10K3MRBD1002
MBD2-MRBD 10K +/- 0.2'C 0-70'C



TE Part #1648596-1
296-0093-01100=CONN,SKT,MARKED

Documents



Product Drawings

TERMINAL,PIDG R 16-14 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-320619-1_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-320619-1_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-320619-1_V.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_8-320619-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_8-320619-1_H.3d_stp.zip

English

Customer View Model

ENG_CVM_8-320619-1_H.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English