**Part Number :** 638084300
**Product Description :** FA2 Mechanical Feed Crimp Applicator for CTX50 Unsealed Small Grip, 0.13mm² Wire
**Series Number :** 207127
**Status :** Active
**Product Category :** Applicators and Crimp Modules




## Documents and Resources

### Tooling Specifications

638084300-000.pdf

TM-638000029-001.pdf

638080200-000.pdf

638080200ES-000.pdf

638080200CN-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Applicators and Crimp Modules |
| Series | 207127 |
| Description | FA2 Mechanical Feed Crimp Applicator for CTX50 Unsealed Small Grip, 0.13mm$^2$ Wire |
| Comments | See Tooling Specification (PDF) Above |
| Function | Crimp |
| Geographic Area | Global |
| Level of Automation | Automatic, Semi-Automatic |
| More Detailed Tech Information | toolingsupport@molex.com |
| Product Name | CTX50,FA2 |
| Tool Type | Applicator |
| UPC | 191130129737 |
| Warranty Disclaimer | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where |

Downloaded from Arrow.com.

| | |
|---|---|
| | Molex Tooling is modified. |

### Physical

| | |
|---|---|
| Net Weight | 1.000/g |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number |
|---|---|
| TM-2000 Universal Press | 638008300 |
| TM-2000 Universal Press (Europe 220V) | 638008400 |
| TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG | 638017200 |
| TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG | 638017300 |
| TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG | 638017600 |
| Use With | Most Industry Standard Presses or Wire Process Machines |

## Applicable Parts

| Description | Part Number |
|---|---|
| CTX50 Receptacle Terminal, Unsealed, Tin Plating, S-Grip, D-Wind, Left Payoff | 5600230444 |
| CTX50 Receptacle Terminal, Unsealed, Tin Plating, S-Grip, D-Wind, Left Payoff | 5600230744 |
| CTX50 Receptacle Terminal, Unsealed, Gold Plating, S-Grip, D-Wind, Left Payoff | 5600230844 |



Downloaded from Arrow.com.