

Product data sheet

Specifications

APC NetShelter Switched Rack PDU, 0U, 10A, 230V, 16 C13 outlet

AP7950B



Overview

Lead time Usually in Stock

Main

Colour	Black
Product or component type	PDU
PDU type	Switched
Cord length	3.05 m
Number of cables	1
Provided equipment	Cord retention bracket(s) Installation guide Rack mounting brackets Toolless mounting kit User manual

Complementary

Input Voltage	200 V 208 V 230 V
Height	124.5 cm
Width	5.6 cm
Output Voltage	230 V
Depth	4.4 cm
Net weight	4.32 kg
Mounting location	Rear
Mounting preference	No preference
Input Plug Type	IEC 60320 C14
Mounting mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
permissible voltage	200...240 V
Max line current	10 A
Input current limits	10 A
Load capacity	2300 VA
Network frequency	47...63 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Outlet type and quantity	16 IEC 60320 C13
--------------------------	------------------

Environment

Product certifications	CE GOST IRAM VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3
Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0...15240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	213.4 cm
Package 1 Width	12.7 cm
Package 1 Length	15.2 cm
Package 1 Weight	5.23 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	1735
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACH Regulation	REACH Declaration
Halogen-free status	Product contains halogen above thresholds

Energy efficiency

Energy Efficiency Optimized	Energy efficient product
-----------------------------	---------------------------------

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
Removable battery	Yes
Take-back	Yes
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

