

6.0 mm×3.5 mm Square Light Touch Switches


Japan

Type: **EVQPJ**

6.0 mm×3.5 mm size, narrow width type

■ Features


- 6.0 mm×3.5 mm-type for space saving, high-density mounting
- Excellent clear click feeling
- Wave soldering available
- Excellent soldering heat endurance due to heat-resistant resin
- Excellent mounting efficiency with radial taping package



■ Recommended Applications

- Car Audio Equipment
- Compact Disc Players
- Operating switches for Electronic Equipment

■ Explanation of Part Numbers




■ Product Chart

Operating Force Type	Bulk Type	SMD	Radial Taping	Height
1.0 N±0.5 N	EVQPJA	EVQPJS	EVQPJG	H=4.3 mm H=5.0 mm
1.6 N±0.5 N	EVQPJB	EVQPJX	EVQPJH	
2.4 N±0.6 N	EVQPJC	EVQPJU	EVQPJJ	






Design, Specifications are subject to change without notice. Ask factory for technical specifications before purchase and/or use. Whenever a doubt about safety arises from this product, please inform us immediately for technical consultation without fail.





■ Major Specifications

Type	Snap action/Push-on type SPST		
Electrical	Circuit Diagram		
	Rating	50 mA 12 Vdc	
	Contact Resistance	100 mΩ max.	
	Insulation Resistance	100 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	10 ms max.	
Mechanical	Operating Force	1.0 N±0.5 N (Low force type) 1.6 N±0.5 N (Standard)	2.4 N±0.6 N
	Travel	0.25 mm ^{+0.20} _{-0.10} mm	
Endurance	Operating Life	50000 cycles min.	30000 cycles min.
	Operating Temperature	-30 °C to +85 °C	
	Storage Temperature	-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)	
Minimum Quantity/ Packing Unit	EVQPJA EVQPJB EVQPJC	1000 pcs. (Vinyl Bag)	
	EVQPJS EVQPJX EVQPJU	2000 pcs. (Reel Pack) (H = 5.0 mm)	2500 pcs. (Reel Pack) (H = 4.3 mm)
	EVQPJG EVQPJH EVQPJJ	2000 pcs. (Radial Taping)	
Quantity/Carton	EVQPJA EVQPJB EVQPJC	10000 pcs.	
	EVQPJS EVQPJX EVQPJU	10000 pcs. (H = 5.0 mm)	12500 pcs. (H = 4.3 mm)
	EVQPJG EVQPJH EVQPJJ	20000 pcs.	

Design, Specifications are subject to change without notice. Ask factory for technical specifications before purchase and/or use.
Whenever a doubt about safety arises from this product, please inform us immediately for technical consultation without fail.


■ Dimensions in mm (not to scale)

No. 1 Japan EVQPJA EVQPJB EVQPJC (Bulk) 					    Circuit diagram  Recommended PWB piercing plan (Pitch tolerance: ±0.1) View from mounting side				
Part Numbers		Operating Force		Height		Knob Color		Operating Life	
EVQPJA04Q		1.0 N		4.3 mm		Grey		50000 cycles	
EVQPJA05Q		1.0 N		5.0 mm		Grey		50000 cycles	
EVQPJB04K		1.6 N		4.3 mm		Black		50000 cycles	
EVQPJB05K		1.6 N		5.0 mm		Black		50000 cycles	
EVQPJC04T		2.4 N		4.3 mm		Brown		30000 cycles	
EVQPJC05T		2.4 N		5.0 mm		Brown		30000 cycles	

No. 2 Japan EVQPJS EVQPJX EVQPJU (Embossed Taping) 6 mm×3.5 mm Square SMD 					    Circuit diagram  Recommended land pattern				
Part Numbers		Operating Force		Height		Knob Color		Operating Life	
EVQPJS04K		1.0 N		4.3 mm		Black		50000 cycles	
EVQPJS05K		1.0 N		5.0 mm		Black		50000 cycles	
EVQPJX04M		1.6 N		4.3 mm		Natural		50000 cycles	
EVQPJX05M		1.6 N		5.0 mm		Natural		50000 cycles	
EVQPJU04K		2.4 N		4.3 mm		Black		30000 cycles	
EVQPJU05K		2.4 N		5.0 mm		Black		30000 cycles	


Design, Specifications are subject to change without notice. Ask factory for technical specifications before purchase and/or use.
Whenever a doubt about safety arises from this product, please inform us immediately for technical consultation without fail.

■ Dimensions in mm (not to scale)


No. 3 Japan EVQPJG EVQPJH EVQPJJ (Radial Taping)  Recommended PWB piercing plan (Pitch tolerance: ±0.1) View from mounting side Circuit diagram				
Part Numbers	Operating Force	Height	Knob Color	Operating Life
EVQPJG04Q	1.0 N	4.3 mm	Grey	50000 cycles
EVQPJG05Q	1.0 N	5.0 mm	Grey	50000 cycles
EVQPJH04K	1.6 N	4.3 mm	Black	50000 cycles
EVQPJH05K	1.6 N	5.0 mm	Black	50000 cycles
EVQPJJ04T	2.4 N	4.3 mm	Brown	30000 cycles
EVQPJJ05T	2.4 N	5.0 mm	Brown	30000 cycles

Design, Specifications are subject to change without notice. Ask factory for technical specifications before purchase and/or use.
Whenever a doubt about safety arises from this product, please inform us immediately for technical consultation without fail.

■ Recommended Reflow Soldering Conditions




● Embossed Carrier Taping



Unit: mm												
Part No.	Height	A	B	W	F	E	P ₁	P ₂	P ₀	D ₀ Dia.	t ₁	t ₂
EVQPJS	4.3/5.0	4.45±0.20	7.25±0.20	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 ^{+0.1} ₀	0.30±0.05	4.5/5.2±0.2
EVQPJX												
EVQPJU												

● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	$\phi 370.0 \pm 2.0$	$\phi 50.0$ min.	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	2.0 ± 0.5

Item	W	T	t	r
Rate (mm)	14.0 ± 1.5	—	1.0 to 3.0	1.0 ± 0.5