




Part Number : [2005062011](#)

Product Description : stAK50h 2 Bay Right-Angle Hybrid Header, 54 Circuits, Bay 1: 27 Circuits/Key 1/ Black; Bay 2: 27 Circuits/Key 2/Green; Tube

Series Number : 200506

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2005062011_sd.pdf](#)

[2005028100-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2005060000-AS-000.pdf](#)

[2005060000-AS-CH-000.pdf](#)

[1600140001-000.pdf](#)


[2005060001-PS-000.pdf](#)

[2005060001-PS-CH-000.pdf](#)

[2005000280-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	200506
Description	stAK50h 2 Bay Right-Angle Hybrid Header, 54 Circuits, Bay 1: 27 Circuits/Key 1/Black; Bay 2: 27 Circuits/Key 2/Green; Tube
Application	Automotive, Power, Signal, Wire-to-Board
Component Type	PCB Header
Product Name	stAK50h
UPC	191130010912

Electrical

Current - Maximum per Contact	5.0A, 12.0A
Voltage - Maximum	14V DC

Physical

Breakaway	No
Circuits (Loaded)	54
Circuits (maximum)	54
Color - Resin	Black, Green
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	20.800/g
Number of Rows	5
Orientation	Right Angle
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm, 4.00mm
Pitch - Termination Interface	2.00mm, 4.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	Yes
Temperature Range - Operating	-40° to +105°C LV-214, -40° to +85°C GMW3191 June2012
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
stAK50h Hybrid Receptacle, 27 Circuits, Key 1, Black, Bag	<u>1600290011</u>
stAK50h Hybrid Receptacle, 27 Circuits, Key 2, Light Green, Bag	<u>1600290012</u>

This document was generated on May 14, 2026