





PRODUCT NUMBER	PITCH
VMxx55x200J0G	5.08 mm



Material:

- Item a Clamp: Steel zinc plated.
- Item b Terminal screw: Steel Zinc plating "-" slot type
- Item c Female contact: High conductivity copper Tin plated
- Item d With flange screw: Steel zinc plated M2.5 "+" slot type
- Item e Terminal (top body): Thermoplastic (UL94V-0)
- Item f Terminal (bottom body): Thermoplastic (UL94V-0)
- Item g Clampage: Steel Zinc plated

Electrical cULus/TUV

- Voltage rating: 300VAC/300VAC
- Current rating: 20A/20A
- Wire range: 0.34-2.5mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In / 0.4Nm
- Screw: M2.5
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: us TUV

N = Number of poles
 Dim L=(N-1)×5.08+15.24
 Dim A=N×5.08+0.5
 Dim B=(N-1)×5.08
 Dim C=(N-1)×5.08+10.16
 Dim D=N×5.08

poles	Tolerance
2P-6P	±0.20
7P-12P	±0.25
13P-18P	±0.30
19P-24P	±0.40

PART NO.: VM xx 55 x 2 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
02	2 poles	Black (RAL9005)	
03	3 poles	Red (RAL3001/D)	
...	...	Orange(RAL2011/P)	
24	24 poles	Yellow(RAL1018/A)	
...	...	Green(RAL6018/T)	
...	...	Blue (RAL5015/A)	
...	...	Grey(RAL7035/D)	
...	...	White(RAL1102)	
...	...	Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family		
ltr	ecn	no	dr	date	tolerances unless otherwise specified	angles	TERMINAL BLOCK		
					X.±0.5	MM	title		
					X.X±0.3		TERMINAL BLOCK		
					X'±1"		PLUGGABLE PLUG, WITH FLANGE		
					dr	EVIN ZHONG 042114	dwg no		
					enr	EVIN ZHONG 042114	sheet 1 of 1 size		
					chr	HANKE FENG 042114	VMxx55x200J0G		
					appd	SHI JUN 042114	A4		
sheet index				revision	A		type		
				sheet	1		CUSTOMER Drawing		