

Han SC module, female with 4 ferrules




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 004 4711
Specification	Han SC module, female with 4 ferrules
HARTING eCatalogue	https://b2b.harting.com/09140044711

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® SC module
Size of the module	Single module
Description of the module	with ceramic ferrule

Version

Gender	Female
Number of contacts	4
Details	Please order contacts separately. Please order fixing plate separately.

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance
Since 1945

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
Approvals	DNV GL

Commercial data

Packaging size	2
Net weight	12 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140020207
ETIM	EC000438
eCl@ss	27440219 Module for industrial connectors (FO)