



Part Number : [1202530607](#)

Product Description : Contrinex Inductive Sensor, 4mm Diameter Smooth Fully Stainless Steel, 3mm Operating Distance, Non-embeddable, PNP, NO, 0.2m 3-wire PUR Cable, 3-pin M8 Connector, 30mm Housing Length

Series Number : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric Sensors

Engineering Number : DW-AV-713-04-276



Documents & Resources

Specifications

[1202530601-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, 4mm Diameter Smooth Fully Stainless Steel, 3mm Operating Distance, Non-embeddable, PNP, NO, 0.2m 3-wire PUR Cable, 3-pin M8 Connector, 30mm Housing Length
IP Rating	IP68, IP69K
Product Name	Contrinex
Type	Inductive
UPC	191130064366

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 1200 Hz

Physical

Connection	Cable (PUR 0.2m, 3-wire), Connector (M8, 3-pin)
Length	30mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel

Mounting Style	Non-embeddable
Net Weight	666.000/g
Operating Distance	3mm
Output	NO
Sensor Housing Size	4mm dia. (smooth)
Temperature Range - Operating	-25° to +85°C

This document was generated on Sep 18, 2025