

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1553219007

Status:

Active

Overview:

Flamar Standard and Custom Cables for Industrial Automation

Description:

Flamar Feedback Cable, WSOR Jacket, Braided Shielding Overall, 12 Circuits, 4x(2x0.34mm²) + 4x(0.50mm²) / 4x(2x22 AWG) + 4x(21 AWG), 9.50mm (.374") Diameter, 200.0m (656.17') Length, Green

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E172949
General	
Product Family	Cable
Series	155321
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Servo Motor
UPC	889056461153
Physical	
Bending Radius - Minimum	> 10xOD
Cable Length	200.0m
Circuits (Loaded)	12 (8+4)
Color - Cable Jacket	Green
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.130/kg
Outer Jacket Diameter	9.50mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	21, 22
Wire Size mm²	0.34, 0.50
Wire/Cable Type	UL AWM 21215 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V
Material Info	
Engineering Number	1X200M



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

155321 Series

Use With

Brad M23 120230 , 120233

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION