



PART NUMBER
10163639-001



NOTE:
TERMINAL HAND CRIMPING TOOL

1. AWG RANGE : 28 AWG
2. FOR CRIMP DETAILS PLEASE REFER
APPLICATION SPEC : GS-20-0704

APPLICATION RANGE:

TOOL PART NUMBER	AWG RANGE	TERMINAL SERIES	TERMINAL PART NUMBER	CONDUCTOR CRIMP HEIGHT	CONDUCTOR CRIMP WIDTH	INSULATION CRIMP HEIGHT	INSULATION CRIMP WIDTH
10163639-001	28	10161952	10161952-YXXXLF	0.55-0.65	0.98-1.08	1.53REF	1.50REF

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family MINITEK POWER			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
A	-	VIPIN	2022-08-23	angles	linear	mm	HAND CRIMPING TOOL			
				0°±2°		scale 1:1	FOR MINITEK POWER PCIE TERMINALS			
				dr	VIPIN M.G	2022-08-23	dwg no	sheet 1 of 1	size	
				enr	MITHUN PAUL	2022-08-23	10163639			A3
				chr	MITHUN PAUL	2022-08-23				
				app	SPK	2022-08-23				
sheet index	revision sheet	A 1					type Product Customer Drawing			