


**Part Number :** [639025800](#)

**Product Description :** FineAdjust Applicator for Micro-Fit 3.0 and Micro-Fit Plus Terminals, for 0.75mm<sup>2</sup> and 18 AWG (UL1061) Wires with Insulation Diameter 1.40-1.85mm

**Series Number :** 207127

**Status :** Active

**Product Category :** Applicators and Crimp Modules



---

## Documents and Resources

### Tooling Specifications

[ATS-639025800-001.pdf](#)

[TM-638000029-001.pdf](#)

[TM-638004900-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Micro-Fit 3.0 and Micro-Fit Plus Terminals, for 0.75mm <sup>2</sup> and 18 AWG (UL1061) Wires with Insulation Diameter 1.40-1.85mm
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust
Tool Type	Applicator
UPC	887191653440
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling

	support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
--	--

## Physical

Net Weight	4996.000/g
------------	------------

## Mates With / Use With

### Use with Part(s)

Description	Part Number
TM-2000 Universal Press	<a href="#">638008300</a>
TM-2000 Universal Press (Europe 220V)	<a href="#">638008400</a>
TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG	<a href="#">638017200</a>
TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG	<a href="#">638017300</a>
TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG	<a href="#">638017600</a>
Use With	Most Industry Standard Presses or Wire Process Machines

## Applicable Parts

Description	Part Number
Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<a href="#">430300038</a>
Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside	<a href="#">430300039</a>

Diameter, Reel	
Micro-Fit 3.0 Crimp Terminal, Female, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430300040</u>
Micro-Fit 3.0 Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430310021</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430310022</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430310023</u>
Micro-Fit High-Current RMF Crimp Terminal, Female, 2.540µm Bright Tin Plating, 18 AWG	<u>2039510001</u>

---

This document was generated on Jun 04, 2026