

P105LF4QLK

Power MOSFETs

40V, 105A, N-channel


Feature

- N-channel
- Small SMD
- Large Current
- Low Ron
- 4.5V Gate Drive
- Low Capacitance
- Based on AEC-Q101
- Halogen free
- Pb free terminal
- RoHS:Yes


OUTLINE

Package (House Name): LF

Package (JEDEC Code): MO-235B similar



Equivalent circuit



Absolute Maximum Ratings (unless otherwise specified : Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Storage temperature	Tstg		-55 to 175	°C
Channel temperature	Tch		-55 to 175	°C
Drain-source voltage	V _{DSS}		40	V
Gate-source voltage	V _{GSS}		±20	V
Continuous drain current(DC)	I _D		105	A
Continuous drain current(Peak)	I _{DP}	Pulse width 10μs, duty=1/100	315	A
Total power dissipation	P _T		168	W
Single avalanche current	I _{AS}	Starting Tch=25°C Tch ≤ 150°C	41	A
Single avalanche energy	E _{AS}	Starting Tch=25°C Tch ≤ 150°C	183	mJ

※ : See the original Specifications


Electrical Characteristics (unless otherwise specified : Tc=25°C)

Item	Symbol	Conditions	Ratings			Unit
			MIN	TYP	MAX	
Drain-Source breakdown voltage	$V_{(BR)DSS}$	ID=1mA, VGS=0V	40			V
Zero gate voltage drain current	I_{DSS}	VDS=40V, VGS=0V			1	μA
Gate-source leakage current	I_{GSS}	VGS=±20V, VDS=0V			±0.1	μA
Forward transconductance	g_{fs}	ID=52.5A, VDS=10V	20			S
Static drain-source on-state resistance	$R_{DS(ON)}$	ID=52.5A, VGS=10V		0.0021	0.0027	Ω
Static drain-source on-state resistance	$R_{DS(ON)}$	ID=52.5A, VGS=4.5V		0.0032	0.0043	Ω
Gate threshold voltage	Vth	ID=1mA, VDS=10V	1.5	2	2.5	V
Source-drain diode forward voltage	V_{SD}	IS=105A, VGS=0V			1.5	V
Thermal resistance	Rth(j-c)	Junction to case, with heatsink ※			0.89	°C/W
Total gate charge	Qg	VDD=32V, VGS=10V, ID=105A		76		nC
Gate to source charge	Qgs	VDD=32V, VGS=10V, ID=105A		15.5		nC
Gate to drain charge	Qgd	VDD=32V, VGS=10V, ID=105A		23		nC
Input capacitance	Ciss	VDS=25V, VGS=0V, f=1MHz		4090		pF
Reverse transfer capacitance	Crss	VDS=25V, VGS=0V, f=1MHz		246		pF
Output capacitance	Coss	VDS=25V, VGS=0V, f=1MHz		492		pF
Turn-on delay time	td(on)	ID=52.5A, RL=0.38Ω, VDD=20V, Rg=0Ω, VGS(+)=10V, VGS(-)=0V		6		ns
Rise time	tr	ID=52.5A, RL=0.38Ω, VDD=20V, Rg=0Ω, VGS(+)=10V, VGS(-)=0V		20		ns
Turn-off delay time	td(off)	ID=52.5A, RL=0.38Ω, VDD=20V, Rg=0Ω, VGS(+)=10V, VGS(-)=0V		83		ns
Fall time	tf	ID=52.5A, RL=0.38Ω, VDD=20V, Rg=0Ω, VGS(+)=10V, VGS(-)=0V		31		ns
Diode reverse recovery time	trr	IF=105A, VGS=0V, di/dt=100A/μs		41		ns
Diode reverse recovery charge	Qrr	IF=105A, VGS=0V, di/dt=100A/μs		45		nC


※ : See the original Specifications

CHARACTERISTIC DIAGRAMS


Typical output characteristics




Transfer characteristics







Static drain-source on-state resistance vs drain current




Static drain-source on-state resistance vs case temperature







Power derating – case temperature



Gate charge characteristics








Single avalanche energy derating vs channel temperature




G7

JEDEC Code	MO-235B similar
JEITA Code	-
House Name	LF



Referential Soldering Pad



Notes

1. If you wish to use any such product, please be sure to refer to the specifications issued by Shindengen.
2. All products described or contained herein are designed with a quality level intended for use in standard applications requiring an ordinary level of reliability. If these products are to be used in equipment or devices for special or specific applications requiring an extremely high grade of quality or reliability in which failures or malfunctions of products may directly affect human life or health, a local Shindengen office must be contacted in advance to confirm that the intended use of the product is appropriate. Shindengen products are grouped into the following three applications according to the quality grade.
 - 【Standard applications】
Computers, office automation and other office equipment, communication terminals, test and measurement equipment, audio/visual equipment, amusement equipment, consumer electronics, machine tools, personal electronic equipment, industrial equipment, etc.
 - 【Special applications】
Transportation equipment (vehicles, ships, etc.), trunk-line communication equipment, traffic signal control systems, anti-disaster/crime systems, safety equipment, medical equipment, etc.
 - 【Specific applications】
Nuclear reactor control systems, aircraft, aerospace equipment, submarine repeaters, life support equipment and systems, etc.
3. Although Shindengen continuously endeavors to enhance the quality and reliability of its products, customers are advised to consider and take safety measures in their design, such as redundancy, fire containment and anti-failure, so that personal injury, fires, or societal damages can be prevented.
4. Please note that all information described or contained herein is subject to change without notice due to product upgrades and other reasons. When buying Shindengen products, please contact the Company's offices or distributors to obtain the latest information.
5. Shindengen shall not bear any responsibility with regards to damages or infringement of any third-party patent rights and other intellectual property rights incurred due to the use of information on this website.
6. The information and materials on this website neither warrant the use of Shindengen's or any third party's patent rights and other intellectual property rights, nor grant license to such rights.
7. In the event that any product described or contained herein falls under the category of strategic products controlled under the Foreign Exchange and Foreign Trade Control Law of Japan, exporting of such products shall require an export license from the Japanese government in accordance with the above law.
8. No reprinting or reproduction of the materials on this website, either in whole or in part, is permitted without proper authorization from Shindengen.