

## ELUA2016OGB 0.08W



### Introduction

The ELUA2016OGB product series is a ceramic based LED with high quality and reliability that suitable for UV application.

### Features

- ◆ Low power UVA LED
- ◆ Dimension 2.04mm\*1.64mm\*0.75mm
- ◆ ESD protection up to 2KV
- ◆ RoHS compliant
- ◆ Pb free
- ◆ EU REACH compliant
- ◆ Halogen Free compliant
- ◆ (Br<900ppm,Cl<900ppm,Br+Cl<1500ppm)

### Applications

- ◆ UV Nail
- ◆ UV Counterfeit
- ◆ UV Catch mosquitoes

## Product Nomenclature

# ELUA2016OGB-PXXXXYY3038020-VA1M

EL = Everlight

UA = UVA

2016 = 2.0mm x 1.6mm Package

O = Package Material: Al<sub>2</sub>O<sub>3</sub>

G = Coating: Ag

B = Angle: 120°

P = Peak Wavelength

XXXX = Wavelength Range [1]

YY = Minimum Radiant Flux Spec [2]

3038 = Forward Voltage Spec: 3.0~3.8V

020 = Forward Current: 20mA

V = Chip Type: Vertical

A = Internal Code

M = Process Type: Molding

## Notes:

### 1. Wavelength Range

Symbol	Description
6070	360~370nm
8090	380~390nm
9000	390~400nm
0010	400~410nm

### 2. Minimum Radiant Flux Spec

Symbol	Description
Q5	25mW

## Absolute Maximum Ratings

Parameter	Symbol	Ratings	Unit
Max. DC Forward Current (mA)	$I_F$	30	mA
Max. ESD Resistance	$V_B$	2000	V
Max. Junction Temperature	$T_J$	105	°C
Operating Temperature	$T_{Opr}$	-40 ~ +85	°C
Storage Temperature	$T_{Stg}$	-40 ~ +85	°C

## PN of the ELUA2016OGB series: UVA LEDs

Order Code of ELUA2016OGB	Minimum Radiant Flux (mW)	Typical Radiant Flux (mW)	Maximum Radiant Flux (mW)	Peak Wavelength (nm)	Forward Voltage (V)	Forward Current (mA)
ELUA2016OGB-P8090Q53038020-VA1M	25	35	45	380~390	3.0~3.8	20
ELUA2016OGB-P9000Q53038020-VA1M	25	35	45	390~400	3.0~3.8	20
ELUA2016OGB-P0010Q53038020-VA1M	25	35	45	400~410	3.0~3.8	20

## Product Binning Radiant Flux Bins

Bin Code	Minimum Radiant Flux (mW)	Maximum Radiant Flux (mW)
Q5	25	45

### Notes:

- 1.Radiant flux measurement tolerance:  $\pm 10\%$ .
- 2.Forward voltage bins are defined at  $I_f=20\text{mA}$  operation.

## Peak Wavelength Bins

Group	Bin	Minimum Peak Wavelength (nm)	Maximum Peak Wavelength (nm)
U	38	380	390
	39	390	400
	40	400	410

### Notes:

- 1.Peak Wavelength measurement tolerance:  $\pm 1\text{nm}$ .
- 2.Forward voltage bins are defined at  $I_f=20\text{mA}$  operation.


## Forward Voltage Bins

Bin	Minimum Forward Voltage (V)	Maximum Forward Voltage (V)
3032	3.0	3.2
3234	3.2	3.4
3436	3.4	3.6
3638	3.6	3.8

### Notes:

- 1.Forward voltage measurement tolerance:  $\pm 2\%$ .
- 2.Forward voltage bins are defined at  $I_f=20\text{mA}$  operation.

## Mechanical Dimension




1. Dimensions are in millimeters.
2. Tolerances unless mentioned are  $\pm 0.1$  mm

## Reflow Soldering Characteristics

### For Reflow Process


- ELUA series are suitable for SMT processes.
- Curing of glue in oven must be according to standard operation flow processes.




Profile Feature	Lead Free Assembly
Ramp-Up Rate	2-3 °C/S
Preheat Temperature	150-200 °C
Preheat Time ( $t_s$ )	60-120 S
Liquid Temperature ( $T_L$ )	217 °C
Time maintained above $T_L$	60-90 S
Peak Temperature ( $T_p$ )	240±5 °C
Peak Time ( $t_p$ )	Max 20 S
Ramp-Down Rate	3-5 °C/S

- Reflow soldering should not be done more than twice.
- In soldering process, stress on the LEDs during heating should be avoided.
- After soldering, do not bend the circuit board.


**Typical Characteristics Curves**  
**Spectrum @ Thermal Pad Temperature = 25°C**




**Relative Radiant Flux vs. Forward Current**  
**@ Thermal Pad Temperature = 25°C**




**Peak Wavelength vs. Forward Current**  
**@ Thermal Pad Temperature = 25°C**




**Forward Voltage vs. Forward Current**  
**@ Thermal Pad Temperature = 25°C**



**Forward Voltage vs. Ambient Temperature**  
**@ Forward Current = 20mA**




**Derating Curve**



### Typical Radiation Patterns

#### Typical Diagram Characteristics of Radiation for ELUA2016OGB




#### Notes:

1.  $2\theta_{1/2}$  is the off axis angle from lamp centerline where the luminous intensity is 1/2 of the peak value.
2. View angle tolerance is  $\pm 5^\circ$ .

## Emitter Tape Packaging

Carrier Tape Dimensions as the following:

Reel: 2000pcs




Unit = mm


### Notes:

1. Tolerance unless mentioned is  $\pm 0.1$ mm
2. Packing amount is 500/1000/1500/2000 pcs per reel

## Moisture Resistant Packaging



## Emitter Reel Dimensions




### Notes:

1. Dimensions are in millimeters.
2. Tolerances unless mentioned are  $\pm 0.1\text{mm}$ .

## Label Explanation

CPN: Customer Specification (when required)  
 P/N : Everlight Production Number  
 QTY: Packing Quantity  
 CAT: Luminous Flux (Brightness) Bin  
 HUE: Color Bin  
 REF: Forward Voltage Bin  
 LOT No: Lot Number  
 MADE IN TAIWAN: Production Place

## Product Labeling



## Storage Conditions

- Before the package is opened. The LEDs should be stored at 30°C or less and 90%RH or less after being shipped from EVERLIGHT and the storage life limits are 12 months.
- After opening the package: The LED's floor life is unlimited under 30°C or less and 85% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
- If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment: 60±5°C for 24 hours.

## DISCLAIMER

- EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized EVERLIGHT sales agent for special application request.