Pushing Performance
Since 1945

Han B Hood Side Entry LC 2 Levers PG 21



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 016 1530
Specification	Han B Hood Side Entry LC 2 Levers PG 21
HARTING eCatalogue	https://harting.com/09300161530

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® B
Type of hood/housing	Hood
Type	Low construction

Version

Size	16 B
Version	Side entry
Number of cable entries	1
Cable entry	1x Pg 21
Locking type	Double locking lever (on the hood)
Han-Easy Lock®	Yes
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP66 IP67

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Technical characteristics

Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
PFAS	Yes
PFAS substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	230 g

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Commercial data

Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140046290
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.