




**Part Number :** [150261280](#)  
**Product Description :** 0.50mm Pitch Premo-Flex  
LVDS Jumper, 305.00mm Cable Length, Gold (Au)  
Plating, 80 Circuits  
**Series Number :** 15026  
**Status :** Active  
**Product Category :** Flat-Flexible Cable (FFC)



## Documents & Resources

### Drawings


- [150261280 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

### Specifications

- [150260001-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15026
Description	0.50mm Pitch Premo-Flex LVDS Jumper, 305.00mm Cable Length, Gold (Au) Plating, 80 Circuits
Product Name	Premo-Flex LVDS Jumper
UPC	195842679900

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V AC

**Physical**

Cable Length	305.00mm
Circuits (Loaded)	80
Contact Layout Type	A (same side)
Design Feature	High-Speed
Material - Outer Jacket	Polyimide
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector
Wire/Cable Type	Flat Cable

Wire Size (AWG)	N/A
-----------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC One-Touch Connector, 0.50mm Pitch, Right-Angle, Bottom Contact, 4.46mm Height, 105°C Operating Temperature, 80 Circuits, Gold (Au) Plating, with Ground Terminal	<u><a href="#">2004850680</a></u>
Easy-On FFC/FPC One-Touch Connector, 0.50mm Pitch, Vertical, 5.60mm Height, 105°C Operating Temperature, 80 Circuits, Gold (Au) Plating, with Ground Terminal	<u><a href="#">2004850780</a></u>

---

This document was generated on Sep 22, 2025