

Part Number : 2153300310
Product Description : Mini-Fit Jr. Female-to-Mini-Fit Jr. Female Off-the-Shelf (OTS) Overmolded Cable Assembly, Single Row, 1.0m Length, 3 Circuits, Black
Series Number : 215330
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2153300310_sd.pdf

Specifications

4000358161-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	215330
Description	Mini-Fit Jr. Female-to-Mini-Fit Jr. Female Off-the-Shelf (OTS) Overmolded Cable Assembly, Single Row, 1.0m Length, 3 Circuits, Black
Application	Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Jr.-to-Mini-Fit Jr.
Product Name	Mini-Fit Jr.
Type	Overmolded Assembly
UPC	193264926015

Electrical

Current - Maximum per Contact	6.0A

Physical

Cable Length	1.0m
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon

Downloaded from Arrow.com.

Net Weight	92.055/g
Number of Rows	1
Overmolded	Yes
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	0.889µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 2464
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Plug Housing, Single Row, 3 Circuits, UL 94V-0, with Panel Mounting Ears, Natural	39014033
Mini-Fit Jr. Plug Housing, Single Row, 3 Circuits, UL 94V-0, without Panel Mounting Ears, Natural	39014037
Mini-Fit Jr. Vertical Header, 4.20mm Pitch, Single Row, 3 Circuits, with Snap-in Plastic Peg PCB Lock, Tin, Natural	39302030
Mini-Fit Jr. Header, Single Row, Right-Angle, with Snap-in Plastic Peg PCB Lock, 3 Circuits, PA Polyamide Nylon 6/6, 94V-0, Tin (Sn) Plating	39303036
Mini-Fit TPA2 Plug Housing, 4.20mm Pitch, Single Row, UL 94V-0, Low-Halogen, Panel Mount, 3 Circuits	2004880003
Mini-Fit TPA2 Plug Housing, 4.20mm Pitch, Single Row, UL 94V-0, Low-Halogen, Old Panel Mount Style, 3 Circuits	2004881003
Mini-Fit TPA2 Plug Housing,	2004881103

Downloaded from Arrow.com.

4.20mm Pitch, Single Row, UL 94V-2, Glow-Wire Capable, Panel Mount, 3 Circuits	
Mini-Fit TPA2 Plug Housing, 4.20mm Pitch, Single Row, UL 94V-0, Low-Halogen, 3 Circuits	2004710003

Downloaded from Arrow.com.