

## M12 CAT5 Bu gerade HWM



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 381 2805
Specification	M12 CAT5 Bu gerade HWM
HARTING eCatalogue	<a href="https://harting.com/21033812805">https://harting.com/21033812805</a>

### Identification

Category	Connectors
Series	Circular connectors M12
Element	PCB adapter
Specification	Straight incl. housing for rear mounting
Description of hood/housing	Long version

### Version

Termination method	Reflow soldering termination (THR)
Gender	Female
Shielding	Unshielded
Number of contacts	8
Coding	X-coding
Locking type	Screw locking
Pack contents	60 pieces in a tray

### Technical characteristics

Rated current	0.5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III



Pushing Performance  
 Since 1945

## Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	2 Nm Lock nut
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 100$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Isolation group	IIIa ( $175 \leq \text{CTI} < 400$ )

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-109
----------------	-----------------



**Pushing Performance**  
Since 1945

## Specifications and approvals

UL / CSA UL 1977 ECBT2.E102079  
CSA-C22.2 No. 182.3 ECBT8.E102079

PROFINET	Yes
----------	-----

## Commercial data

Packaging size	60
----------------	----

Net weight	27.78 g
------------	---------

Country of origin	Romania
-------------------	---------

European customs tariff number	85366990
--------------------------------	----------

GTIN	5713140138247
------	---------------

eCl@ss	27460201 PCB connector (board connector)
--------	--

ETIM	EC002637
------	----------

UNSPSC 24.0	39121415
-------------	----------