


4

3

2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		A	RELEASED	18 JUN 08	K.M	S.Y




Technical Specifications

- **Workable Cable Types** : Coaxial cables, Multi-core cables, Standard cables
- **Stripping Length** : 0.01 - 40.00 mm
- **Stripping Diameter** : 0.00 - 2.20 ϕ mm
- **Stripping Steps** : Max. 9
- **Cable Gripping** : Motor-driven, 10 phase programmable
- **Production Rate** : 600 /Hr (Varies with programming)
- **Processing Data Capacity** : 1000 cables processing data
- **PC Interface** : RS232C
- **Noise Level** : 50 dB
- **Power Supply** : AC 100 - 240 V
- **Dimensions** : 136 x 690 x 260 mm
- **Net Weight** : Approx. 10 kg

(Specifications subject to change without notice.)

Note: Recommended to conduct a sufficient pre-purchase test, as exceptions may apply to some cable types.
Contact our local representative with processing specifications.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. MARUYAMA 18 JUN 08		Tyco Electronics Tyco Electronics Corporation Kawasaki, Japan											
		CHK H. TANAKA 18 JUN 08													
DIMENSIONS: 単位： 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD H. TANAKA 18 JUN 08		NAME 名称 MICRO COAXIAL STRIPPER COSMIC 42R									
				PRODUCT SPEC 製品規格 —											
				APPLICATION SPEC 取付適用規格 —											
				WEIGHT —											
				SIZE A3				CAGE CODE 00779		DRAWING NO 番号 C-2047792-1		RESTRICTED TO —			
MATERIAL 材料 —		FINISH 仕上 —		CUSTOMER DRAWING						SCALE 尺度 —		SHEET 1 OF 1		REV A	