

D


- C


- B

- A



SCALE 4.000



NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC (INCHES) AND TOLERANCES ARE: <0.5mm = ±0.05mm <0.020 = ±0.002 >0.5 - 6mm = ±0.1mm >0.020 - 0.236 = ±0.004 >6.00 - 30mm = ±0.2mm >0.236 - 1.181 = ±0.008 >30.00 - 120mm = ±0.3mm >1.181 - 4.725 = ±0.012			MATERIAL SEE NOTES		TITLE 75 OHM 1.0/2.3 STR JACK PCB MOUNT WITH 3 LEGS		Amphenol RF			
THIRD ANGLE PROJ. 			REFERENCE			ENGINEER S.L.I		DATE 23-MAR-11		SHEET NO. 2 OF 2		SCALE: 14.0:1.0	
EAR#			ANGLES = ±1°			SIZE B		DRAWING NO. 1236251B1-004-3GT10G-75		REV B			
						ITEM NO. 106251ABBA1ER7F		PART NO. 282127-75-10					