

T H E R M O M E T R I C S
A C O M M I T M E N T T O E X C E L L E N C E

NTC Type NK

Thermometrics Epoxy-Coated Chip Thermistor



Description

A range of NTC chip thermistors with solder-coated steel wires and epoxy resin coating.

Features

- Designed for accurate temperature measurement, control and compensation
- AEC-Q200 qualified
- Tight tolerances on resistance and B value
- Operation up to 311°F (155°C) with excellent stability
- Small body diameter
- Fast response
- Suitable for automotive, HVAC and white goods applications
- Limited heat conduction along steel wires
- Available on bandolier to IEC 286-2

Amphenol
Advanced Sensors

Type NK Specifications

Chip thermistor with solder-coated wires


Ordering Information

Replace * in the codes shown above as follows:

- Loose-packed: R
- Bandoliered: B

Options

- Other resistance values within the ranges shown;
- e.g. code NK701C2*2 for $700 \Omega \pm 2\%$ at 77°F (25°C)
- Reference temperatures other than 77°F (25°C)
- Wire lengths 0.47 in to 1.57 in (12 mm to 40 mm) (± 1 mm)



NTC Type NK Dimensions

Data

- Minimum operating temperature: -40°F (-40°C)
- Maximum operating temperature: See table
- Thermal time constant: 15s (cooling)
- 2.4 s (ambient change)
- Dissipation factor: 2.2 mW/K
- Mass: 0.00040 lbs (0.18 g)
- Packing/MOQ: 1000/box (loose)
2000/reel (bandoliered)

R25 Ω	Material System	B25/125 K	Maximum Operating Temperature °F (°C)	Code R25°C $\pm 1\%$	Code R25°C $\pm 2\%$	Code R25°C $\pm 3\%$	Code R25°C $\pm 5\%$	Code R25°C $\pm 10\%$
500	2	$3540 \pm 1\%$	257 (125)		NK501C2*2	NK501C2*3	NK501C2*5	NK501C*R10
1000	2	$3540 \pm 1\%$	257 (125)		NK102C2*2	NK102C2*3	NK102C2*5	NK102C2*10
2000	2	$3540 \pm 1\%$	257 (125)		NK202C2*2	NK202C2*3	NK202C2*5	NK202C2*10
500	2A	$3627 \pm 1\%$	257 (125)		NK501C2A*2	NK501C2A*3	NK501C2A*5	NK501C2A*10
1000	2A	$3627 \pm 1\%$	257 (125)		NK102C2A*2	NK102C2A*3	NK102C2A*5	NK102C2A*10
2000	2A	$3627 \pm 1\%$	257 (125)		NK202C2A*2	NK202C2A*3	NK202C2A*5	NK202C2A*10
2200	1	$3977 \pm 0.75\%$	311 (155)	NK222C1*1	NK222C1*2	NK222C1*3	NK222C1*5	NK222C1*10
2700	1	$3977 \pm 0.75\%$	311 (155)	NK272C1*1	NK272C1*2	NK272C1*3	NK272C1*5	NK272C1*10
5000	1	$3977 \pm 0.75\%$	311 (155)	NK502C1*1	NK502C1*2	NK502C1*3	NK502C1*5	NK502C1*10
10000	1	$3977 \pm 0.75\%$	311 (155)	NK103C1*1	NK103C1*2	NK103C1*3	NK103C1*5	NK103C1*10
2200	3	$3960 \pm 1\%$	311 (155)			NK222C3*3	NK222C3*5	NK222C3*10
2700	3	$3960 \pm 1\%$	311 (155)			NK272C3*3	NK272C3*5	NK272C3*10
5000	3	$3960 \pm 1\%$	311 (155)			NK502C3*3	NK502C3*5	NK502C3*10
10000	3	$3960 \pm 1\%$	311 (155)			NK103C3*3	NK103C3*5	NK103C3*10
5000	4A	$3435 \pm 1\%$	230 (110)	NK502C4*A1	NK502C4*A2	NK502C4*A3	NK502C4*A5	NK502C4*A10
10000	4A	$3435 \pm 1\%$	230 (110)	NK103C4*A1	NK103C4*A2	NK103C4*A3	NK103C4*A5	NK103C4*A10
10000	5	$3540 \pm 1.5\%$	230 (110)	NK103C5*1	NK103C5*2	NK103C5*3	NK103C5*5	NK103C5*10
12000	5	$3540 \pm 1.5\%$	230 (110)	NK123C5*1	NK123C5*2	NK123C5*3	NK123C5*5	NK123C5*10

See separate tables for resistance - temperature data.

Amphenol
Advanced Sensors

www.amphenol-sensors.com

© 2014 Amphenol Corporation. All Rights Reserved. Specifications are subject to change without notice.
Other company names and product names used in this document are the registered trademarks or
trademarks of their respective owners.

AAS-920-573B-03/2014