


VS-507

Description

The VS-507 VCSO (Voltage Controlled Saw Oscillator) is an ultra high frequency, ultra low phase noise oscillator. The VS-507 provides 10fs rms jitter in a 12kHz to 20MHz integration bandwidth and is available from 3 to 6 GHz.

Features

- Frequency Range 3.0 to 6.0 GHz
- Ultra low jitter performance
- Typical Jitter: 10fsec rms, 12kHz to 20MHz
- 3.3V supply voltage
- Output: Sinewave & Balanced Sinewave
- 9x14 mm SMD package
- See table on Page 5 for standard frequencies

Applications

- High Speed ADCs
- 100G & 400G Coherent Receivers
- 5G BTS
- Test & Measurement
- Military

Performance Specifications


Pulling Characteristics					
Parameter	Min	Typ	Max	Units	Notes
Absolute Pull Range (APR)	±5			ppm	Includes df vs: •Operating temperature range -40 .. 85°C •Aging 10 years •Supply Voltage Change 5% •Load change 10%
Tuning Slope	Positive				
Control Voltage Range	0	1.65	3.3	V DC	with $V_s = 3.3V$
Frequency control input impedance	100			kΩ	
Modulation bandwidth	20			kHz	@ -3dB
Supply Voltage (V_s)					
Supply voltage (standard)	3.135	3.3	3.465	V DC	
Current consumption			85	mA	

Performance Specifications (Continued)

RF Output					
Parameter	Min	Typ	Max	Units	Notes
Signal	Sinewave				
Load	45	50	55	Ω	
Output Power	0	3	6	dBm	
Signal	Balanced Sinewave				
Load	45	50	55	Ω	
Output Power	0	3	6	dBm	
Phase Noise: 100Hz offset		-54		dBc/Hz	@ 5.89824GHz Sinewave 3.3V
Phase Noise: 1kHz offset		-86		dBc/Hz	
Phase Noise: 10kHz offset		-112		dBc/Hz	
Phase Noise: 100kHz offset		-134		dBc/Hz	
Phase Noise: 1MHz offset		-146		dBc/Hz	
Phase Noise: 10MHz offset		-149		dBc/Hz	
Jitter: 12kHz to 20MHz offset		10		fs rms	

Additional Parameters					
Parameter	Min		Max	Units	Notes
Weight	2.0g				
Subharmonics			-25	dBc	
Processing and Packing	Handling and Processing Note				
Absolute Maximum Ratings					
Parameter	Min		Max	Units	Notes
Supply Voltage (V _s)			6.0	V	
Operable Temperature Range	-40		+85	°C	
Storage Temperature Range	-40		+95	°C	

Typical Performance




Outline Drawing / Enclosure

Package Codes		
Code	Height "H"	Pin Length "L"
G218C	2.8	N/A

Dimensions in mm


Pin Assignment Sinewave	
1	Control Voltage (V_c)
2	GND
3	GND
4	RF Out
5	N.C.
6	Supply Voltage Input (V_s)

Pin Assignment Balanced Sinewave	
1	Control Voltage (V_c)
2	GND
3	GND
4	RF Out
5	RF-Out Compl. (180° phase shifted)
6	Supply Voltage Input (V_s)



Marking
VS-507-xxxx
Frequency
•AYYWW

Standard Shipping Method



Dimension in mm:

A, B and K are dependent upon component dimensions

production tolerance complying DIN IEC 286-3

All dimensions in millimeters unless otherwise stated

Enclosure Type	Tape Width W (mm)	Quantity per meter	Quantity per reel	Dimension P (mm)
G218C	24		1700	12

Recommended Reflow Profile


TP: max 250°C (@ solder joint, customer board level)

T_p: max: 10...30 sec

Additional Information:

This SMD oscillator has been designed for pick and place reflow soldering

SMD oscillators must be on the top side of the PCB during the reflow process.



Ordering Information

VS - 507 1 - E E E - 506 X - 5898M24000

Product Family
VS: VCSO

Package
9x14mm SMT

Height
0: 2.8mm (G218C)

Supply Voltage
E: +3.3V

RF Output Code
E: Sinewave
F: Balanced Sinewave

Temperature Range
E: -40°C to +85°C

APR Code
506: ±5ppm

Frequency
Enable
X: No Enable

Standard Frequencies (MHz)

3137.95842	3328	3468.75	3494.061674	3799.904088	3922.418236	3973.638766
4000	4096.9586	4137.350272	4270.747196	4800	4915.2	5898.24

Other frequencies and temperature ranges available upon request

Notes:

1. Contact factory for improved stabilities or additional product options. Not all options and codes are available at all frequencies.
2. Unless other stated all values are valid after warm-up time and refer to typical conditions for supply voltage, frequency control voltage, load, temperature (25°C).
3. Phase noise degrades with increasing output frequency.
4. Subject to technical modification.
5. Contact factory for availability.

Contact Information

USA:

100 Watts Street
Mt Holly Springs, PA 17065
Tel: 1.717.486.3411
Fax: 1.717.486.5920

Europe:

Landstrasse
74924 Neckarbischofsheim
Germany
Tel: +49 (0) 7268.801.0
Fax: +49 (0) 7268.801.281



Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATION OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING, BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly, or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip and Vectron names and logos are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

Rev. 16 Febr. 2023