

Specification Sheet

Part Number: 151-06500



H-profile of the saddles allows for broad surface contact with the bundle, which minimizes pinching and crushing of the bundle.

Swivels in 360-degree motion to accommodate any area.

Accommodates T50–T250 ties to handle both light-duty and heavy-duty applications.

Dual Swivel Saddle Spacer for T50-T250, 0.25 - 3.0" Bundle Diameter, PA66HS/POM, Black, 2200/pkg

Article Number	151-06500
----------------	-----------

Type	DSWS4
------	-------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	These saddle spacers are installed between two bundles (such as wires, cables, hoses, tubing, conduit, etc.) to separate and prevent chafing and wear. The mounts can be easily rotated by hand, allowing the bundles to be crossed and rotated at any angle. Cable ties, which secure the bundles, are used with the mounts. The dual swivel saddle spacers accommodate cable ties up to 1/2" wide.
---------------------	--

Short Description	Dual Swivel Saddle Spacer for T50-T250, 0.25 - 3.0" Bundle Diameter, PA66HS/POM, Black, 2200/pkg
-------------------	--

Global Part Name	DSWS4-PA66HS/POM-BK
------------------	---------------------

Length L (Imperial)	0.91
---------------------	------

Length L (Metric)	23.6
-------------------	------

Width W (Imperial)	0.8
--------------------	-----

Width W (Metric)	20.3
------------------	------

Bundle Diameter Min (Imperial)	0.3
--------------------------------	-----

Bundle Diameter Min (Metric)	6.0
------------------------------	-----

Bundle Diameter Max (Imperial)	3.0
--------------------------------	-----

Bundle Diameter Max (Metric)	76.0
------------------------------	------

Cable Ties	T50 - T250
------------	------------

Height H (Imperial)	0.7
---------------------	-----

Height H (Metric)	18.0
-------------------	------

Cable Tie Width Max (Imperial)	0.5
--------------------------------	-----

Cable Tie Width Max (Metric)	12.7
------------------------------	------

Material	Polyamide 6.6 heat stabilized (PA66HS) Polyacetal (POM)
Material Shortcut	PA66HS POM
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C) -31°F to +185°F (-35°C to +85°C)
Minimum Extraction Force (Imperial)	100.0
Minimum Extraction Force (Metric)	445
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2200
Package Quantity (Metric)	2200
Customs Number	3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)
[RoHS/WEEE Compliance](#)
[Disclaimer](#)
[Terms and Conditions](#)