


## 48-78W, 18 to 60V or 36 to 75V Input Isolated DC-DC Eighth Brick

<https://product.tdk.com/en/power/iEA>  
[www.emea.lambda.tdk.com/iEA](http://www.emea.lambda.tdk.com/iEA)



Industrial



Test



COMM



Broadcast

The iEA series of isolated DC-DC converters deliver up to 78W in a compact industry eighth brick footprint. Available in 36-75V or 18-60V inputs with single outputs from 5V, 12V, 15V, 18V and 28V, these converters are designed primarily for use in 48V and 24V input bus architectures in communications, test and measurement, and industrial applications. Its single board open frame design allows the iEA series to achieve a low profile design of 8.81mm max to support tight board-to-board spacing and still provide high useable power at elevated ambient temperatures.

### Features

- High Operating Efficiency up to 90.5%
- Open Frame, Single Board Construction
- Constant Switching Frequency
- -40 to 125 °C Operating Temperature With Minimal Derating

### Benefits

- Reduces Heat Losses/Dissipation in System
- Low Profile for Tight Board to Board Spacing
- Predictable EMI
- High Useable Power At Elevated Ambient Temperature

### Model Selector

| Model                               | Input Voltage (V) | Output Voltage (V) | Maximum Current (A) | Maximum Power (W) | On/Off Polarity | Efficiency, Full Load (typ) | Pin Length (inch) |
|-------------------------------------|-------------------|--------------------|---------------------|-------------------|-----------------|-----------------------------|-------------------|
| <a href="#">IEA48003A280V-001-R</a> | 36 - 75           | 28                 | 2.67                | 75                | Neg             | 90%                         | 0.145             |
| <a href="#">IEA48003A280V-005-R</a> | 36 - 75           | 28                 | 2.67                | 75                | Neg             | 90%                         | 0.200             |
| <a href="#">IEA48004A180V-001-R</a> | 36 - 75           | 18                 | 3.75                | 68                | Neg             | 90.5%                       | 0.145             |
| <a href="#">IEA48005A150V-001-R</a> | 36 - 75           | 15                 | 4.5                 | 68                | Neg             | 90%                         | 0.145             |
| <a href="#">IEA48007A120V-000-R</a> | 36 - 75           | 12                 | 6.5                 | 78                | Pos             | 90.5%                       | 0.145             |
| <a href="#">IEA48007A120V-001-R</a> | 36 - 75           | 12                 | 6.5                 | 78                | Neg             | 90.5%                       | 0.145             |
| <a href="#">IEA48007A120V-005-R</a> | 36 - 75           | 12                 | 6.5                 | 78                | Neg             | 90.5%                       | 0.200             |
| <a href="#">IEA48015A050V-000-R</a> | 36 - 75           | 5                  | 15                  | 75                | Pos             | 90%                         | 0.145             |
| <a href="#">IEA48015A050V-001-R</a> | 36 - 75           | 5                  | 15                  | 75                | Neg             | 90%                         | 0.145             |
| <a href="#">IEA4W004A120V-003-R</a> | 18 - 60           | 12                 | 4                   | 48                | Neg             | 91%                         | 0.110             |

### Related Products


| Type                         | Part Number                    | Description                                                                                           |
|------------------------------|--------------------------------|-------------------------------------------------------------------------------------------------------|
| Isolated DC-DC Converter     | <a href="#">iQL</a>            | 300W, Input 36-75V or 18-36V, Isolated Quarter Brick                                                  |
| Isolated DC-DC Converter     | <a href="#">iQG</a>            | 300W~504W, Input 36-75V, Isolated Quarter Brick                                                       |
| Isolated DC-DC Converter     | <a href="#">iEH</a>            | 300W, Input 36-75V, Isolated Eighth Brick                                                             |
| Isolated DC-DC Converter     | <a href="#">GQA</a>            | 120W Industrial, Input 9-36V, Isolated Quarter Brick                                                  |
| Non-Isolated DC-DC Converter | <a href="#">iBH</a>            | 80W/20A, 3.5-14Vin, 0.7 - 5.5Vout, DOSA Compatible                                                    |
| Non-Isolated DC-DC Converter | <a href="#">iCH</a>            | 85W/12A, 4.5-14Vin, 0.7 - 8.5Vout, DOSA Compatible                                                    |
| Input Filter                 | <a href="#">iDQ</a>            | 75V / 10A Filter                                                                                      |
| Evaluation Board             | <a href="#">FQX-HQA-EVK-D0</a> | Evaluation board (no modules) accepting standard Eighth or Quarter brick and FQx or iDQ input filters |

| Specifications                            |      |                                                                                  |               |               |               |               |               |
|-------------------------------------------|------|----------------------------------------------------------------------------------|---------------|---------------|---------------|---------------|---------------|
| Model                                     |      | 5V                                                                               | 12V (iEA48)   | 12V (iEA4W)   | 15V           | 18V           | 28V           |
| Input                                     |      |                                                                                  |               |               |               |               |               |
| Input Voltage Range                       | Vdc  | 36 - 75                                                                          |               | 18 - 60       | 36 - 75       |               |               |
| Input Transient (100 ms)                  | Vdc  | 100                                                                              |               | 72            | 100           |               |               |
| Input Current (max)                       | A    | 4                                                                                |               | 5             | 4             |               |               |
| Turn-On Input Voltage (typ)               | Vdc  | 33                                                                               |               | 17            | 33            |               |               |
| Turn-Off Input Voltage (typ)              | Vdc  | 30                                                                               |               | 15.5          | 30            |               |               |
| Efficiency (typical)                      | %    | See Model Selector Table                                                         |               |               |               |               |               |
| Safety Certifications and Markings        | -    | IEC/UL/CSA/EN 62368-1, 60950-1, CE Mark and UKCA Mark                            |               |               |               |               |               |
| Output                                    |      |                                                                                  |               |               |               |               |               |
| Output Voltage Initial Setpoint           | Vdc  | 4.92 - 5.08                                                                      | 11.64 - 12.36 | 11.64 - 12.36 | 14.55 - 15.45 | 17.5 - 18.5   | 27.16 - 28.84 |
| Output Voltage Tolerance                  | Vdc  | 4.85 - 5.15                                                                      | 11.58 - 12.42 | 11.52 - 12.48 | 14.47 - 15.52 | 17.28 - 18.72 | 26.88 - 29.12 |
| Line Regulation (typ)                     | mV   | 2                                                                                | 10            |               |               |               | 20            |
| Load Regulation (typ)                     | mV   | 1                                                                                | 10            |               |               |               | 15            |
| External Load Capacitance                 | uF   | 0 - 5000                                                                         | 0 - 2000      | 200 - 2000    | 0 - 1500      | 0 - 1000      | 0 - 470       |
| Ripple & Noise (typ)                      | mVpp | 55                                                                               | 80            | 75            | 40            | 50            | 80            |
| Switching Frequency (fixed)               | kHz  | 400                                                                              | 400           | 215           | 300           | 375           | 450           |
| Overcurrent Protection Threshold (Hiccup) | A    | 20                                                                               | 8.5           | 5.5           | 6             | 4.4           | 4             |
| Over Voltage Protection                   | Vdc  | 5.7 - 6.7                                                                        | 13.6 - 15.7   | 16.5          | 16.8 - 22     | 20 - 26       | 32-38         |
| Over Temperature Protection               | -    | Auto recovery                                                                    |               |               |               |               |               |
| Environmental                             |      |                                                                                  |               |               |               |               |               |
| Operating Temperature (Tc)                | °C   | -40 to 125                                                                       |               |               |               |               |               |
| Storage Temperature                       | °C   | -55 to 125                                                                       |               |               |               |               |               |
| Humidity (non condensing)                 | %RH  | 10 - 95                                                                          |               |               |               |               |               |
| Cooling                                   | -    | Conduction, convection or forced air (See product specifications for derating)   |               |               |               |               |               |
| Isolation Voltage (Input to Output)       | Vdc  | 1500                                                                             |               |               |               |               |               |
| Isolation Resistance                      | MΩ   | ≥10                                                                              |               |               |               |               |               |
| Shock                                     | -    | MIL-STD-202G, Method 213B, Test Condition 1                                      |               |               |               |               |               |
| Vibration                                 | -    | 5 to 50 Hz (0.5g); 50 to 500 Hz (1.5g); three axes; Bellcore TR-EOP-000063-5.4.4 |               |               |               |               |               |
| Other                                     |      |                                                                                  |               |               |               |               |               |
| Weight (max)                              | g    | 30.4                                                                             |               |               |               |               |               |
| Size (LxWxH)                              | inch | 2.3 x 0.9 x 0.347                                                                |               |               |               |               |               |
|                                           | mm   | 58.42 x 22.86 x 8.81                                                             |               |               |               |               |               |
| MTBF - Telcordia SR-332 (100% Load, 40°C) | MHrs | > 4.8                                                                            |               |               |               |               |               |
| Warranty                                  | yrs  | 3                                                                                |               |               |               |               |               |


## Notes

See website for detailed product specifications and test methods

## Mechanical Specification iEA48 Series



## Recommended PCB Hole Pattern iEA48 Series




## PIN Assignment iEA48 Series


| Pin | Function | Pin | Function |
|-----|----------|-----|----------|
| 1   | Vin(+)   | 5   | Sense(-) |
| 2   | On/Off   | 6   | Trim     |
| 3   | Vin(-)   | 7   | Sense(+) |
| 4   | Vo(-)    | 8   | Vo(+)    |

Pin base material is brass with tin plating.

## Mechanical Specification iEA4W Series



## Recommended PCB Hole Pattern iEA4W Series



## PIN Assignment iEA4W Series

| Pin | Function | Pin | Function |
|-----|----------|-----|----------|
| 1   | Vin(+)   | 4   | Vo(-)    |
| 2   | On/Off   | 8   | Vo(+)    |
| 3   | Vin(-)   |     |          |

Pin base material is brass with gold over nickel plating.

**TDK-Lambda France SAS**

Tel: +33 1 60 12 71 65  
france@fr.tdk-lambda.com  
www.emea.lambda.tdk.com/fr

**Italy Sales Office**

Tel: +39 02 61 29 38 63  
info.italia@it.tdk-lambda.com  
www.emea.lambda.tdk.com/it

**Netherlands**

info@nl.tdk-lambda.com  
www.emea.lambda.tdk.com/nl

**TDK-Lambda Germany GmbH**

Tel: +49 7841 666 0  
info@de.tdk-lambda.com  
www.emea.lambda.tdk.com/de

**Austria Sales Office**

Tel: +43 2256 655 84  
info@at.tdk-lambda.com  
www.emea.lambda.tdk.com/at

**Switzerland Sales Office**

Tel: +41 44 850 53 53  
info@ch.tdk-lambda.com  
www.emea.lambda.tdk.com/ch

**Nordic Sales Office**

Tel: +45 8853 8086  
info@dk.tdk-lambda.com  
www.emea.lambda.tdk.com/dk

**TDK-Lambda UK Ltd.**

Tel: +44 (0) 12 71 85 66 66  
info@uk.tdk-lambda.com  
www.emea.lambda.tdk.com/uk

**TDK-Lambda Ltd.**

Tel: +9 723 902 4333  
info@tdk-lambda.co.il  
www.emea.lambda.tdk.com/il

**C.I.S.****Commercial Support:**

Tel: +7 (495) 665 2627

**Technical Support:**

Tel: +7 (812) 658 0463  
info@tdk-lambda.ru  
www.emea.lambda.tdk.com/ru

**TDK-Lambda Americas**

Tel: +1 800-LAMBDA-4 or 1-800-526-2324  
powersolutions@us.tdk-lambda.com  
www.us.lambda.tdk.com

**TDK Electronics do Brasil Ltda**

Tel: +55 11 3289-9599  
sales.br@tdk-electronics.tdk.com  
www.tdk-electronics.tdk.com/en

**TDK-Lambda Corporation**

Tel: +81-3-6778-1113  
www.jp.lambda.tdk.com

**TDK-Lambda (China) Electronics Co. Ltd.**

Tel: +86 21 6485-0777  
powersolutions@cn.tdk-lambda.com  
www.lambda.tdk.com.cn

**TDK-Lambda Singapore Pte Ltd.**

Tel: +65 6251 7211  
tis.mkt@sg.tdk-lambda.com  
www.sg.lambda.tdk.com

**TDK India Private Limited, Power Supply Division**

Tel: +91 80 4039-0660  
mathew.philip@in.tdk-lambda.com  
www.sg.lambda.tdk.com

