



Pushing Performance  
Since 1945

# DSUB SV FE TSDP STR 15P AU3



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 015 4754
Specification	DSUB SV FE TSDP STR 15P AU3
HARTING eCatalogue	<a href="https://harting.com/09670154754">https://harting.com/09670154754</a>

## Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector
Description of the contact	Turned Straight

## Version

Termination method	Wave soldering termination
Gender	Female
Size	D-Sub 2
Connection type	Motherboard to daughtercard Mezzanine
Number of contacts	15
Termination length	5.8 mm
PCB fixing	Without board locks
Locking type	Fixing flange with feed through hole Ø 3.1 mm

## Technical characteristics

Distance between rows	2.84 mm
Contact spacing (termination side)	2.74 mm
Flange height	6.5 mm
Rated current	7.5 A
Clearance distance	≥1 mm



**Pushing Performance**  
Since 1945

## Technical characteristics

Creepage distance	≥1 mm
Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤10 mΩ
Limiting temperature	-55 ... +125 °C
Insertion force	≤50 N
Withdrawal force	≥4.5 N ≤33 N
Performance level	3
Mating cycles	≥50
Test voltage U <sub>r.m.s.</sub>	1 kV
Isolation group	IIIa (175 ≤ CTI < 400)
PCB thickness	≥1.6 mm
Installation height	5.4 mm
Hot plugging	No

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Shell: steel, tin plated
Colour (insert)	White
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)



Pushing Performance  
Since 1945

Material properties

Requirement set with Hazard Levels R26

Specifications and approvals

Specifications	DIN 41652
UL / CSA	UL 1977 ECBT2.E102079

Commercial data

Packaging size	50
Net weight	11.8 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140090828
eCl@ss	27440214 D-Sub coupler
ETIM	EC001136
UNSPSC 24.0	39121469