











# SMT Gate Drive Transformer

1500Vdc Basic and Operational Insulation.  
Ruggedized

**PulseR**  
Ruggedized Solutions



-  Maximum Reflow Temperature: +235°C
-  Storage Temperature: -55°C to +130°C
-  Moisture Sensitivity Level : 3
-  1500 V<sub>DC</sub> isolation between Gate and Drive
-  Basic Insulation (1.4mm creepage/clearance) and operational available
-  Part designed for rugged environments
-  Construction techniques assure excellent resistance to vibration and shock
-  Operating frequency: 50kHz and up
-  Tape and Reel packaging available
-  Lead Finish: SnPb

## Electrical Specifications @ 25°C — Operating Temperature -55°C to +130°C



Part Number	Turns Ratio	Pri-Sec Isolation (V <sub>DC</sub> )	MAX <sup>1</sup> V* $\mu$ sec	Primary Inductance (mH MIN)	Leakage <sup>2</sup> Inductance ( $\mu$ H MAX)	DCR Primary ( $\Omega$ MAX)	DCR Secondary ( $\Omega$ MAX)	Package Size (L x W x H) (mm MAX)
X-1569	1:1:1	1500	45.1	3.3	0.700	1.6	1.6	9.0 x 8.6 x 7.6

- NOTES: 1. The maximum volt-sec rating limits the flux density to 2200 Gauss when used in a unipolar drive application. For bi-polar drive applications a maximum volt-sec of two time this rating is acceptable. (2\*(volt\* sec ratio))
2. Leakage Inductance is measured at the primary terminals with all secondaries shorted.
3. Add suffix "T" to part number for Tape & Reel package.
4. To order a RoHS compliant part, add the suffix "NL" to the part number, i.e. X-1569 becomes X-1569NL.

## Electrical Schematic

## Schematic

X-1569



Part hardened for aerospace use.

Weight.....1.22grams  
Pan/Tube Size=50


# SMT Gate Drive Transformer

1500Vdc Basic and Operational Insulation.

Ruggedized

**PulseR**  
Ruggedized Solutions

## Tin/Lead Recommended Reflow Profile (Based on J-STD-020D)



$T_{SMIN}$ (°C)	$T_{SMAX}$ (°C)	$T_L$ (°C)	$T_P$ (°C MAX)	$t_s$ (s)	$t_L$ (s)	$t_p$ (s MAX)	Ramp-up rate ( $T_L$ to $T_P$ )	Ramp-down rate ( $T_P$ to $T_L$ )	Time 25°C to peak temperature (s MAX)
100	150	183	235	60-120	60-150	20	3°C/s MAX	6°C/s MAX	360

Notes:

1. All temperatures measured on the package leads.
2. Maximum times of reflow cycle: 2.

## For More Information

PulseR North America  
Headquarters  
311 Sinclair Road,  
Bristol, PA 19007-1524  
U.S.A.

Tel: +1.215. 781. 6400  
Fax: +1.215. 781. 6403

For Global Sales Representative and Locations Visit:  
<http://www.pulseruggedized.com>

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2019. PulseR, LLC. All rights reserved.