

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622030575

Status:

Active

Overview:

Application Tooling

Description:

Impact Backplane Press-In Tool

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	887191189642
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622030575, TM-622018799



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

76845 Impact 100 Ohm Vertical Orthogonal Backplane Signal Module Assembly, 4-Pair by 8 Column

Application Tooling Description	FAQ Product #
Impact 100 Ohm 4 Pair Vertical Orthogonal Header, Dual Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, 0.254µm Gold	1713481828
Impact 100 Ohm 4 Pair Vertical Orthogonal Header, Unguided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole	768451805

Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 768451807
4 Pair Vertical
Orthogonal Header,
Unguided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead Free
Impact 100 Ohm 768451824
4 Pair Vertical
Orthogonal Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 768451825
4 Pair Vertical
Orthogonal Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 768451827
4 Pair Vertical
Orthogonal Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 768451828
4 Pair Vertical
Orthogonal Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 768453805
4 Pair Vertical
Orthogonal Header,
Left Guide, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 768453807
4 Pair Vertical
Orthogonal Header,

Left Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead Free
Impact 100 Ohm 768453808
4 Pair Vertical
Orthogonal Header,
Left Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead Free
Impact 100 Ohm 768455807
4 Pair Vertical
Orthogonal Header,
Right Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead Free
Impact 100 Ohm 768457804
4 Pair Vertical
Orthogonal Header,
Left Guide, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 768457805
4 Pair Vertical
Orthogonal Header,
Left Guide, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 768457807
4 Pair Vertical
Orthogonal Header,
Left Guided, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead Free
Impact 100 Ohm 768457808
4 Pair Vertical
Orthogonal Header,
Left Guide, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole

Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 768459804
4 Pair Vertical
Orthogonal Header,
Right Guide, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 768459807
4 Pair Vertical
Orthogonal Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead Free
Impact 100 Ohm 768459808
4 Pair Vertical
Orthogonal Header,
Right Guide, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free

This document was generated on 11/23/2020
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION