

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	1/4/09	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 7 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 2 thru 12
 A = .156 [3.96] x No. of Positions
 B = .156 [3.96] x No. of Spaces

ADAM TECH

909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

156 [3.96] POWER HEADER
 STRAIGHT, WITH REAR LOCK

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]				TITLE			
TOLERANCES: EXCEPT AS NOTED				156 [3.96] POWER HEADER			
INCHES				STRAIGHT, WITH REAR LOCK			
Holes				SIZE			
.X	± .10	ØXX	± .10	PART NO.			
.XX	± .020	ØXXX	± .015	LHC-XX-TS-V0			
.XXX	± .015	ØXXX	± .010	REV.			
APPROVALS				SCALE: NTS			
DATE				SHEET 1 OF 1			
DRAWN	SS	1/4/09					
CHECKED							
APPROVED							

A

B

C

D

6

5

4

3

2

1