






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E4	REV AS	PER ECR-23-169592	17MAR2023	DP	HW

D




- 1 MATERIAL: HOUSING: POLYESTER. COLOR: GRAY. UL 94V-0. CONTACT: COPPER ALLOY.
- 2 FINISH: IN ACCORDANCE WITH PRODUCT SPECIFICATION 108-1651, GOLD PLATING OR EQUIVALENT PLATING ON PRODUCT CONTACT MATING AREA, AND MATTE TIN PLATING ON COMPLIANT PIN AREA, ALL OVER MATTE NICKEL UNDERPLATED. DETAIL PLEASE REFER TO PRODUCT SPECIFICATION 108-1651.
- 3 FINISH: CONTACT LUBRICATION WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 4 10.26±0.13 DIMENSION APPLIES IN THIS AREA.
- 5 REFERENCE APPLICATION SPEC 114-1103 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
6. CURRENT RATING 10A/CONTACT PER PRODUCT SPEC 108-1651.

C



SECTION W-W
SCALE 40:1


B



RECOMMENDED PCB HOLE LAYOUT

C	A,B,D,E	-	5	5646955-8
A,B,D	C,E	-	5	5646955-6
A,B,D,E	-	C	5	5646955-5
A - C	D - E	-	5	5646955-4
A	B - E	-	5	5646955-3
E	A - D	-	5	5646955-2
A - E	-	-	5	5646955-1
POSITIONS LOADED WITH 10.90 REF CONTACTS	POSITIONS LOADED WITH 9.30 REF CONTACTS	POSITIONS LOADED WITH 7.68 REF CONTACTS	NO OF LOADED POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARRO 14DEC04	TE Connectivity	
DIMENSIONS: mm		CHK R. PATTERSON 14DEC04	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. PATTERSON 14DEC04	PRODUCT SPEC	
0 PLC ± -		108-1651		
1 PLC ± -		APPLICATION SPEC		
2 PLC ± 0.13		114-1103		
3 PLC ± -		WEIGHT		
4 PLC ± -		0.000000		
ANGLES ± -		SCALE		
FINISH		SHEET		
MATERIAL		CUSTOMER DRAWING		

		ASSEMBLY, RIGHT ANGLE HEADER, W/ RETENTION PEGS, UNIVERSAL POWER MODULE		RESTRICTED TO -
		SIZE CAGE CODE DRAWING NO A1 00779 C5646955		