



NOTE:
1.MATERIAL SPECIFICATION:
1.HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V−0
2.TERMINAL: COPPER ALLOY
3.MID PLATE: STAINLESS STEEL
4.OUT SHELL: STAINLESS STEEL
5.INNER SHELL: STAINLESS STEEL
2.PLATING SPECIFICATION:
2−1.CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON CONTACT AREA
(GOLD PLATING THICKNESS FOLLOW THE P/N DESCRIPTION)
Au 1u" PLATED ON SOLDER AREA
2−2.OUT SHELL&INNER SHELL:
Ni 30u" MIN. UNDER PLATED OVER ALL.
2−3.MID PLATE:
Ni 30u" MIN. UNDER PLATED OVER ALL.
3.MECHANICAL PERFORMANCE,
3−1.INSERTION FORCE: 0.5~2.0kgf.
3−2.REMOVAL FORCE: 0.8kgf~2.0kgf.(INTITIAL)
0.6kgf~2.0kgf.(AFTER DURABILITY TEST)
3−3.DURABILITY: 10000 CYCLES.
4.ELECTRICAL PERFORMANCE,
4−1. VOLTAGE RATING: 20V.
CURRENT RATING: 5A.
4−2. LLCR:
VBUS & GND PINS AND OTHER PINS: 40mΩ/PIN MAX.
LLCR MAX. CHANGE OF ALL PINS: 10mΩ.
4−3.INSULATION RESISTANCE: 100MΩ MIN
4−4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
5. ENVIRONMENTAL PERFORMANCE:
OPERATING TEMPERATURE: −55℃~+85℃.
6.IR REFLOW:
THE PEAK TEMPERATURE ON THE BOARD SHALL
BE MAINTAINED FOR 10 SECONDS AT 260℃.
7.PRODUCT PART NUMBER DESCRIPTION:
10198100 − 0 0 0 X X LF
LEAD FREE
PACKING TYPE:
1: TAPE/REEL
CONTACT AREA PLATING
1: GOLD FLASH

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family HPL 511
ltr	ecn no	dr	date	tolerances unless otherwise specified			
A	-	TY.Tang	2026/03/30	angles 0°±x°	linear 0.X±0.35 0.XX±0.25 0.XXX±0.15	mm scale 1:1	title USB TYPE C 24PIN SMT TYPE
				dr	TY.Tang	2026/03/30	dwg no 10198100 sheet 1 of 2 size A3
				engr	TY.Tang	2026/03/30	
				chr	LQ LEI	2026/03/30	Amphenol FCi
				appd	TIM YAO	2026/03/30	type Product Customer Drawing
sheet index	revision A sheet 1						

© 2016 AFCI


Downloaded from Arrow.com.




SCALE 2:1

RECOMMENDED PCB LAYOUT(TOP VIEW)

Thickness 1.0mm (TOLERANCE=±0.05mm?





USB TYPE−C PIN ASSIGNMENTS

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TXp1	TXn1	VBUS	CC1	D+	D−	SBU1	VBUS	RXn2	RXp2	GND
GND	RXp1	RXn1	VBUS	SBU2	D−	D+	CC2	VBUS	TXn2	TXp2	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection	product family		
ltr	ecn no	dr	date	tolerances unless otherwise specified					HPL 511		
A				angles	linear	0.X±0.35		mm	title		
						0.XX±0.25			USB TYPE C		
				0°±x°		0.XXX±0.15		scale 1:1	24PIN SMT TYPE		
				dr	TY.Tang	2026/03/30			dwg no 10198100	sheet 2 of 2	size A3
				engr	TY.Tang	2026/03/30		Amphenol FCi			
				chr	LQ LEI	2026/03/30			type Product Customer Drawing		
				appd	TIM YAO	2026/03/30					
sheet index	revision sheet	A 2									

© 2016 AFCI

Downloaded from Arrow.com.