



[+ TERMINALS & SPLICES](#)  
[CRIMP TERMINAL HOUSINGS](#)



✓ Active

TE CONNECTIVITY (TE)

## 3P POSITIVE LOCK HSG, MARK II

[Positive Lock | 250](#)

1969760-1

TE Internal Number: 1969760-1

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

**Terminal Style** Receptacle

**Housing Type** Receptacle Housing

**Number of Positions** 3

**Terminal Orientation** Straight

**UL Flammability Rating** UL 94V-0

[↓ PRODUCT DRAWING](#)  
English

### DOCUMENTATION

Product Drawings

#### 3P POSI-LOCK, MARK II

PDF

English

Agency Approvals

UL Report

#### POSITIVE LOCK AND POSITIVE LOCK EX SERIES REPORT

PDF

English

### FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

#### Product Type Features

**Insulated** Yes

**Product Type** Terminal Housing

**Terminates To** Wire/Cable

---

#### Configuration Features

**Number of Positions** 3

---

#### Body Features

**Housing Color** Natural

**Mating Retention** With

**Mating Alignment** With

---

#### Contact Features

**Terminal Style** Receptacle

**Terminal Orientation** Straight

---

#### Mechanical Attachment

**Mating Retention Type** Latch

---

#### Housing Features

**Housing Type** Receptacle Housing

**Housing Material** Nylon

---

#### Dimensions

**Accepts Wire Insulation Diameter Range (in)** .193

---

#### Usage Conditions

**Operating Temperature Range** -40 – 130 °C [ -40 – 266 °F ]

---

#### Industry Standards

**UL Flammability Rating** UL 94V-0

---

#### Packaging Features

**Packaging Method** Box

---

#### Statement of Compliance

**Statement of Compliance**

PDF

