






PRODUCT NUMBER	PITCH
THxx01x000J0G	5.00 mm



Material

- Item ① Clamp: Brass(CuZn) Tin plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Female contact :PhBz (CuSn)
- Item ④ Terminal(housing): Thermoplastic (UL94V-0)

Electrical cULus / TUV / VDE

- Voltage rating: 300V/300V/300V
- Current rating: 15A/15A/12A
- Wire range: 0.34-1.5mm² / 0.34-1.5mm²
- Solid wire(AWG): 14-22 / 14-22
- Stranded wire(AWG): 14-22 / 14-22
- Torque: 3.5Lb-In / 0.4N.m / 0.4N.m
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety Approval:



PART NO.: TH xx 01 x 0 00J0 G

N = Number of poles

Dim A=Nx5.0

Dim B=(N-1)x5.0

poles	Tolerance	
	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.25	±0.15
13-18p	±0.30	±0.20
19-24p	±0.40	±0.30

End Stackable No. of poles	Body Color	RoHS compliant (lead<4%) In copper Alloy
02 2 poles	Black (RAL9005)	
03 3 poles	Red (RAL3001/D)	
...	Orange(RAL2011/P)	
...	Yellow(RAL1018/A)	
24 24 poles	Green(RAL6018/T)	
	Blue (RAL5015/A)	
	Grey(RAL7035/D)	
	White(RAL1102)	
	Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK
					angles		title
					X±0.5	MM	TERMINAL BLOCK
					X.X±0.3		WIRE PROTECTOR,PLUGGABLE PLUG,END STACKABLE
					X*±1"	scale	dwg no
					dr EVIN ZHONG 041614		sheet 1 of 1 size
					enrg EVIN ZHONG 041614		THxx01x000J0G
					chr HANKE FENG 041614		A4
					appd SHI JUN 041614		type
sheet	revision	A					CUSTOMER Drawing
index	sheet	1					